

# MM-WMS 6,4 (EX10)R C1 YE/BK - Shrink sleeve



1116141

<https://www.phoenixcontact.com/us/products/1116141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, Mixed color, unmarked, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, cable diameter range: 2.1 ... 6.4 mm, mounting type: slide-on, Number of individual labels: 1, roll length: 1.8 m, text field height: 8.2 mm, text field width: 1800 mm

## Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- Thanks to the continuous format, a shrink sleeve marker of the appropriate length can be created flexibly for the relevant application
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The shrink sleeve material provides additional electrical insulation and mechanical protection for conductors
- The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- The material is cUL certified



## Commercial data

Item number	1116141
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG221E
GTIN	4063151041618
Weight per piece (including packing)	48.1 g
Weight per piece (excluding packing)	38 g
Customs tariff number	96121010
Country of origin	CN

# MM-WMS 6,4 (EX10)R C1 YE/BK - Shrink sleeve



1116141

<https://www.phoenixcontact.com/us/products/1116141>

## Technical data

### Product properties

Product type	Shrink sleeve
Area of application	Railway industry

### Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	Thermal transfer

### Dimensions

Length of roll	1.80 m
Height	11.2 mm

### Text field

Text field width	1800 mm
Text field height	8.2 mm

### Material specifications

Color	multicolored (RAL -)
	yellow (RAL 1018)
	black (RAL 9005)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	3:1
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 3
Components	free from silicone, halogen, and cadmium

### Cable/line

External cable diameter	2.1 mm ... 6.4 mm
-------------------------	-------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

# MM-WMS 6,4 (EX10)R C1 YE/BK - Shrink sleeve



1116141

<https://www.phoenixcontact.com/us/products/1116141>

Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

## Mounting

Mounting type	slide-on
---------------	----------

# MM-WMS 6,4 (EX10)R C1 YE/BK - Shrink sleeve



1116141

<https://www.phoenixcontact.com/us/products/1116141>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1116141>



**cULus Recognized**  
Approval ID: E310982

# MM-WMS 6,4 (EX10)R C1 YE/BK - Shrink sleeve



1116141

<https://www.phoenixcontact.com/us/products/1116141>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# MM-WMS 6,4 (EX10)R C1 YE/BK - Shrink sleeve



1116141

<https://www.phoenixcontact.com/us/products/1116141>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	3.986 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)