

PLD M 140 W 895/D25 - LED machine light



1118015

<https://www.phoenixcontact.com/us/products/1118015>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LED machine light, 24 V DC, emission angle (vertical/Horizontal): 89 °/97 °, length: 895 mm, diameter: 25 mm, degree of protection: IP54, can be swiveled

Figure shows length variant with 615 mm

Product description

This LED machine light is designed to provide illumination inside or on machinery. The small diameter of just 25 mm enables mounting even where space is at a premium. The mounting accessories included also enable easy mounting on aluminum system profiles. In the mounting brackets supplied, the light can swivel and the lighting can therefore be optimally aligned. The satin-finished plastic cover prevents glare for the machine operator.

Your advantages

- Space saving, thanks to the small diameter
- Plug-in supply line enables free choice of the cable length as well as quick and easy installation
- Focused illumination, thanks to swivel action
- ETL approval permits use on the North American market
- Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 60000 h

Commercial data

Item number	1118015
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR08
Product key	DRL221
GTIN	4063151046316
Weight per piece (including packing)	740 g
Weight per piece (excluding packing)	388 g
Customs tariff number	94054239
Country of origin	DE

PLD M 140 W 895/D25 - LED machine light



1118015

<https://www.phoenixcontact.com/us/products/1118015>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Machine light
Application	Machine
Mounting position	any
Special properties	can be swiveled $\pm 60^\circ$

Electrical properties

Supply: Module electronics

Connection method	M12 connector, A-coded
Number of positions	5
Permissible conductor cross-section	min. 0.34 mm ²
Supply voltage	24 V DC
Supply voltage range	22 V DC ... 26 V DC
Current consumption	typ. 0.75 A (at 24 V DC)
Power consumption	approx. 18 W (at 24 V DC)
Protective circuit	Surge protection; Suppressor diode, 36 V DC Reverse polarity protection; Polarity protection diode

Input data

Digital:

Input name	Digital inputs
Number of inputs	1
Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage U_{IN}	24 V DC
Input frequency	max. 2 Hz

Signaling

Light properties

Source of light type	LED
Number of LEDs	72
Color temperature	≥ 5000 K
Color rendering index	80
Luminous flux	approx. 1890 lm (Net luminous flux)
Luminous efficacy	approx. 105 lm/W
Illumination	max. 671 lx (Distance of 1 m)

PLD M 140 W 895/D25 - LED machine light




1118015

<https://www.phoenixcontact.com/us/products/1118015>

Average illumination	min. 331 lx (Distance of 1 m over 1 m ² area)
Emission angle	508 lx (Distance of 1 m over 1 m ² area)
	89 ° (C0-C180)
	97 ° (C90-C270)
Ordinance	Delegated Regulation (EU) 2019/2015
Energy efficiency class	E (2 light sources)
Note	This product contains energy efficiency class E light sources.

Dimensions

Dimensional drawing	
Width	25 mm
Height	26.5 mm
Length	895 mm
Diameter	25 mm
Note on dimensions	Length without M12 flush-type connector

Material specifications

Color	aluminum color
-------	----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
Degree of protection	IP54
Air pressure (operation)	69 kPa ... 102 kPa
Air pressure (storage/transport)	69 kPa ... 102 kPa
Ambient temperature (storage/transport)	-10 °C ... 50 °C
Permissible humidity (operation)	95 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)

Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	4g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	50g

Energy labeling

Ordinance	Delegated Regulation (EU) 2019/2015
Note (EPREL)	The EPREL entry can be searched for with the registration number (https://eprel.ec.europa.eu/screen/home)
	The EPREL entry can be searched for with the model ID (https://eprel.ec.europa.eu/screen/product/lightsources)

Energy labeling (Light source 1)

Registration number	1097916
Model ID	801096

PLD M 140 W 895/D25 - LED machine light



1118015

<https://www.phoenixcontact.com/us/products/1118015>

Energy efficiency class	E
Number of light sources	1

Energy labeling (Light source 2)

Registration number	1097918
Model ID	801101
Energy efficiency class	E
Number of light sources	1

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	Screw mounting (via supplied mounting brackets and fastening elements)
Mounting position	any

PLD M 140 W 895/D25 - LED machine light




1118015

<https://www.phoenixcontact.com/us/products/1118015>

Drawings

Dimensional drawing



PLD M 140 W 895/D25 - LED machine light



1118015

<https://www.phoenixcontact.com/us/products/1118015>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1118015>



ETLus

Approval ID: LV-Lighting-Systems



cETL

Approval ID: Luminaires



EAC

Approval ID: TR_TS_D_12879-22

PLD M 140 W 895/D25 - LED machine light



1118015

<https://www.phoenixcontact.com/us/products/1118015>

Classifications

ECLASS

ECLASS-13.0	27110345
ECLASS-15.0	27110345

ETIM

ETIM 10.0	EC000348
-----------	----------

UNSPSC

UNSPSC 21.0	32151500
-------------	----------

PLD M 140 W 895/D25 - LED machine light



1118015

<https://www.phoenixcontact.com/us/products/1118015>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5fb1b8b3-e802-4421-a0b2-0ba9deb1336c

EF3.1 Climate Change

CO2e kg	20.45 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com