

# WP 4101-WXPS - Web panel



1148687

<https://www.phoenixcontact.com/us/products/1148687>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Web panel, 25.7 cm / 10.1"-TFT display (projective-capacitive (PCAP)), 1280 x 800 pixel(s) (WXGA), 16.7 million colors, Arm® Cortex®-A53, 4x 1.2 GHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Yocto/Linux®, Chromium Browser, without bus system.

## Your advantages

- Easy startup – just enter the IP and URL
- Flexible, thanks to open web standard and free choice of web server and visualization software
- No security updates are required for JAVA or Flash plug-ins thanks to HTML5
- Ideal for use with PLCnext Engineer or CODESYS
- Embedded Linux operating system
- Visualization of self-programmed JavaScript applications possible
- Secure communication, thanks to SSL-encrypted data transmission

## Commercial data

Item number	1148687
Packing unit	1 pc
Sales key	DR17
Product key	DRCADF
GTIN	4063151141899
Weight per piece (including packing)	1,770 g
Weight per piece (excluding packing)	1,270 g
Customs tariff number	84714100
Country of origin	DE

## Technical data

### Product properties

Product type	Operator panel
Weight	1270 g

### Computer data

Processor	Arm® Cortex®-A53, 4x 1.2 GHz
Operating system	Yocto/Linux®
RAM	1 GB LPDDR3
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

### Display

Display type	25.7 cm / 10.1"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	850 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	85.00 °
Reading angle right	85.00 °
Reading angle top	85.00 °
Reading angle bottom	85.00 °

### Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	Without optional interface
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

### System properties

User software	Chromium Browser
---------------	------------------

### System requirements

Runtime system	Chromium browser
----------------	------------------

### Electrical properties

#### Supply

Supply voltage	24 V DC
Supply voltage range	18 V ... 30 V
Power supply unit	24 V DC ±20 %
Typical current consumption	0.6 A

# WP 4101-WXPS - Web panel



1148687

<https://www.phoenixcontact.com/us/products/1148687>

## Real-time clock

Realtime clock	Integrated (battery backup)
----------------	-----------------------------

## Mounting

Mounting type	Front mounting
---------------	----------------

## Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	20 % ... 85 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

## Dimensions

### External dimensions

Width / Height / Depth	263 mm / 200 mm / 6 mm (Dimensions of the front plate)
------------------------	--

### Installation dimensions

Width / Height / Installation depth	252 mm / 189 mm / 45 mm (Installation cutout)
-------------------------------------	---

# WP 4101-WXPS - Web panel

1148687

<https://www.phoenixcontact.com/us/products/1148687>



## Classifications

### UNSPSC

UNSPSC 21.0	43211900
-------------	----------

1148687

<https://www.phoenixcontact.com/us/products/1148687>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6afb86bb-4222-4d54-8170-7d543c856a60

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)