

HC-M-05-MWF-M - Contact insert module



1118092

<https://www.phoenixcontact.com/us/products/1118092>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 5, power contacts: 5, Pin, Push-in connection, 400 V, 16 A, 0.5 mm² ... 2.5 mm², application: Power, with double function slot for bridges

Module for sleeve housing

Your advantages

- Easy installation without tools, even when mounted, with push-in connection technology
- Function moves into the connector
- Function directly at the application
- Multifunction slot in the module
- Reliable wiring
- Shock-resistant and vibration-resistant

Commercial data

Item number	1118092
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4063151046491
Weight per piece (including packing)	50.84 g
Weight per piece (excluding packing)	50.84 g
Customs tariff number	85366990
Country of origin	CN

HC-M-05-MWF-M - Contact insert module



1118092

<https://www.phoenixcontact.com/us/products/1118092>

Technical data

Notes

General	only use flexible conductors with ferrules
General	Connectors may be operated only when there is no load/voltage.
General	For HEAVYCON housing type B6 to B48, HC-M-B...MF-... module carrier frame required

Product properties

Product type	Modular contact insert
Series	HC-M-05
Application	Power
Number of positions	5
Connection profile	5
No. of power contacts	5
Contact material type	turned
Special properties	Use in HEAVYCON sleeve housing type B6 ... B48

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data

Connection technology

Connection technology	Push-in connection
-----------------------	--------------------

Conductor connection

Conductor cross-section	0.5 mm ² ... 2.5 mm ²
Connection cross section AWG	21 ... 14
Stripping length of the individual wire	10 mm ±1 mm

Dimensions

Dimensional drawing	
Width	33.9 mm
Height	45.5 mm
Length	29.3 mm

Mechanical characteristics

Minimum housing height	72 mm
Contact diameter	2.5 mm

Electrical properties

HC-M-05-MWF-M - Contact insert module



1118092

<https://www.phoenixcontact.com/us/products/1118092>

Rated voltage (III/3)	400 V
Rated surge voltage	4 kV
Rated current	16 A

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

HC-M-05-MWF-M - Contact insert module




1118092


<https://www.phoenixcontact.com/us/products/1118092>


Drawings

Dimensional drawing




Schematic diagram





Derating diagram for flexible conductors



Derating diagram for flexible conductors with ferrule

HC-M-05-MWF-M - Contact insert module



1118092

<https://www.phoenixcontact.com/us/products/1118092>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1118092>

	cULus Recognized Approval ID: E468743			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	20 A	- 14	-

HC-M-05-MWF-M - Contact insert module



1118092

<https://www.phoenixcontact.com/us/products/1118092>

Classifications

ECLASS

ECLASS-13.0	27440217
ECLASS-15.0	27440217

ETIM

ETIM 10.0	EC000438
-----------	----------

HC-M-05-MWF-M - Contact insert module



1118092

<https://www.phoenixcontact.com/us/products/1118092>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com