

CUC-MP-J1ST-A/2R4LT-LED - Modular RJ45 PCB connectors



1149854

<https://www.phoenixcontact.com/us/products/1149854>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x2 multi-port, connection direction of the connector to the PCB: 90 °, Tab up, Shielded, shield springs, LED (yellow, green), number of positions: 8, 10 Gbps, PoE++, THT, THD, Wave, IP20, type of packaging: Tray

Your advantages

- The right version for every application. Available with and without LED, single- and multi-port
- The extended temperature range from -40 °C to +85 °C enables use in demanding applications
- Through-hole technology (THT) provides high mechanical stability when connecting the female connector to the PCB

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1149854 |
| Packing unit | 60 pc |
| Minimum order quantity | 60 pc |
| Sales key | AB12 |
| Product key | ABNADA |
| GTIN | 4063151146214 |
| Weight per piece (including packing) | 10.66 g |
| Weight per piece (excluding packing) | 10.66 g |
| Customs tariff number | 85366930 |
| Country of origin | TW |

CUC-MP-J1ST-A/2R4LT-LED - Modular RJ45 PCB connectors



1149854

<https://www.phoenixcontact.com/us/products/1149854>

Technical data

Product properties

| | |
|---------------------|--|
| Slots | 1x2 multi-port |
| Orientation to PCB | 90.00 ° |
| Type | THD |
| Number of positions | 8 (8P8C) |
| Type of locking | Snap-in locking, Tab up |
| Shielding | Shielded, shield springs |
| Status display | LED (yellow, green) |
| Processing notes | Wave |
| Type of packaging | Tray |
| Transmission speed | 10 Gbps |
| Power transmission | PoE++ (according to IEEE 802.3bt) |
| Power PSE | 90 W (Class 8 in accordance with IEEE 802.3bt) |
| Power PD | 71 W (Class 4 in accordance with IEEE 802.3bt) |

Electrical properties

| | |
|--------------------------------|-------------------------|
| Pollution degree | 2 (IEC 60664-1) |
| Overvoltage category | I (IEC 60664-1) |
| Rated voltage | 72 V DC |
| Rated surge voltage | 1.5 kV DC (IEC 60664-1) |
| Rated current | 1.5 A (IEC 60603-7) |
| Insulation resistance | > 500 MΩ (IEC 60603-7) |
| Test voltage (Contact/contact) | 1.5 kV DC (IEC 60603-7) |
| Test voltage (Contact/shield) | 1.5 kV DC (IEC 60603-7) |

Dimensions

| | |
|------------------|----------|
| Length | 16.25 mm |
| Width | 32.26 mm |
| Height | 19.03 mm |
| Installed height | 13.68 mm |
| Data pin length | 2.54 mm |

Material specifications

| | |
|--|-----------------------|
| Material Contact carrier | PA |
| Flame resistance | UL 94 V0 |
| Halogen-free | no |
| Material Housing | Copper alloy |
| Material Housing coating | Ni (0,508 μm / 20 μ") |
| Material Housing pin coating (top layer/selective) | Ni (0,508 μm / 20 μ") |
| Material Contact | Phosphor bronze |
| Material Solder contact coating (intermediate layer) | Ni (1.27 μm/50 μ") |

CUC-MP-J1ST-A/2R4LT-LED - Modular RJ45 PCB connectors



1149854

<https://www.phoenixcontact.com/us/products/1149854>

| | |
|---|----------------------|
| Material Solder contact coating (top layer/selective) | Sn (2.54 µm/100 µ") |
| Material Plug contact coating (top layer/selective) | Au (0,152 µm / 6 µ") |
| Material Plug contact coating (intermediate layer) | Ni (1.27 µm/50 µ") |

Mechanical properties

Mechanical data

| | |
|-----------------------------|----------------------|
| Insertion/withdrawal cycles | > 750 (IEC 60603-7) |
| Insertion force | < 20 N (IEC 60603-7) |
| Withdrawal force | < 20 N (IEC 60603-7) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Degree of protection (plugged in) | IP20 (IEC 60603-7) |
| Degree of protection (Not plugged in) | IP20 (IEC 60603-7) |

Test specification for vibration - sine

| | |
|--------------|---------------------|
| Acceleration | 50 m/s ² |
| Amplitude | 0.35 mm |
| Sweep speed | 1 octave/min |

Mounting

Processing notes

| | |
|---------------|-----|
| Mounting type | THT |
|---------------|-----|

CUC-MP-J1ST-A/2R4LT-LED - Modular RJ45 PCB connectors



1149854

<https://www.phoenixcontact.com/us/products/1149854>

Drawings



Classification wave soldering profile

CUC-MP-J1ST-A/2R4LT-LED - Modular RJ45 PCB connectors



1149854

<https://www.phoenixcontact.com/us/products/1149854>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1149854>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

CUC-MP-J1ST-A/2R4LT-LED - Modular RJ45 PCB connectors



1149854

<https://www.phoenixcontact.com/us/products/1149854>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002637 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CUC-MP-J1ST-A/2R4LT-LED - Modular RJ45 PCB connectors



1149854

<https://www.phoenixcontact.com/us/products/1149854>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com