

CRIMPFOX 10T-F - Crimping pliers



1134913

<https://www.phoenixcontact.com/us/products/1134913>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 0.14 mm², max. cross section: 10 mm², For TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, frontal insertion, compression: Trapezoidal crimp, weight 302 g, black

Your advantages

- Large cross section range from 0.14 mm² ... 10 mm²
- For ferrules up to a length of 18 mm
- Comfortable to use, thanks to low grip span with optimum manual force progression
- Process reliability, thanks to pressure lock and self-adjusting die
- Suitable for TWIN ferrules, thanks to continuous automatic adjustment

Commercial data

Item number	1134913
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4063151067168
Weight per piece (including packing)	389.4 g
Weight per piece (excluding packing)	301.8 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX 10T-F - Crimping pliers



1134913

<https://www.phoenixcontact.com/us/products/1134913>

Technical data

Product properties

Product type	Crimping tool
Compression	Trapezoidal crimp
Product property	Rotating, self-adjusting crimping die (duo versions)
	Compact, lightweight, and optimally balanced
	Low grip span
	Ergonomic two-component handle
	Low actuation force
	Suitable for TWIN ferrules
	Handle with non-slip pad
	Tool-free unlockable pressure lock

Crimping position 1

Min. cross section	0.14 mm ²
Max. cross section	10 mm ²
AWG min	26
AWG max	8

Electrical properties

Fuse	DIN 46228-1, DIN 46228-4
------	--------------------------

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 10 mm ² (2 x 0.5 mm ² ... 2 x 4 mm ²)
Cross section range AWG	26 ... 8 (2 x AWG 20 ... 2 x AWG 12)

Dimensions

Width	65 mm
Height	25 mm
Length	180 mm

Material specifications

Color	black
-------	-------

CRIMPFOX 10T-F - Crimping pliers



1134913

<https://www.phoenixcontact.com/us/products/1134913>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 10T-F - Crimping pliers



1134913

<https://www.phoenixcontact.com/us/products/1134913>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com