

CUC-SP-J1ST-A/R4LB-SMD - Modular RJ45 PCB connectors



1149874

<https://www.phoenixcontact.com/us/products/1149874>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 90 °, Tab down, Shielded, number of positions: 8, 10 Gbps, PoE++, SMT, SMD, Reflow, IP20, type of packaging: Tape and Reel

Your advantages

- The reflow capability enables efficient, cost-optimized processing
- Tape-on-reel packaging is perfect for automated processing
- The extended temperature range from -40 °C to +85 °C enables use in demanding applications

Commercial data

Item number	1149874
Packing unit	110 pc
Minimum order quantity	110 pc
Sales key	AB12
Product key	ABNADB
GTIN	4063151146337
Weight per piece (including packing)	7.727 g
Weight per piece (excluding packing)	7.727 g
Customs tariff number	85366930
Country of origin	TW

CUC-SP-J1ST-A/R4LB-SMD - Modular RJ45 PCB connectors



1149874

<https://www.phoenixcontact.com/us/products/1149874>

Technical data

Product properties

Slots	1x1 single-port
Orientation to PCB	90.00 °
Type	SMD
Number of positions	8 (8P8C)
Type of locking	Snap-in locking, Tab down
Shielding	Shielded
Processing notes	Reflow
Type of packaging	Tape and Reel
Transmission speed	10 Gbps
Power transmission	PoE++ (according to IEEE 802.3bt)
Power PSE	90 W (Class 8 in accordance with IEEE 802.3bt)
Power PD	71 W (Class 4 in accordance with IEEE 802.3bt)

Electrical properties

Pollution degree	2 (IEC 60664-1)
Overvoltage category	I (IEC 60664-1)
Rated voltage	72 V DC
Rated surge voltage	1.5 kV DC (IEC 60664-1)
Rated current	1.5 A (IEC 60603-7)
Insulation resistance	> 500 M Ω (IEC 60603-7)
Test voltage (Contact/contact)	1.5 kV DC (IEC 60603-7)
Test voltage (Contact/shield)	1.5 kV DC (IEC 60603-7)

Dimensions

Length	20.85 mm
Width	18.1 mm
Height	15 mm
Installed height	11.80 mm

Material specifications

Material Contact carrier	PA
Flame resistance	UL 94 V0
Halogen-free	no
Material Housing	Copper alloy
Material Housing coating	Ni (0,508 μm / 20 μm)
Material Housing pin coating (top layer/selective)	Ni (0,508 μm / 20 μm)
Material Contact	Phosphor bronze
Material Solder contact coating (intermediate layer)	Ni (1.27 μm /50 μm)
Material Solder contact coating (top layer/selective)	Sn (2.54 μm /100 μm)
Material Plug contact coating (top layer/selective)	Au (0,152 μm / 6 μm)

CUC-SP-J1ST-A/R4LB-SMD - Modular RJ45 PCB connectors



1149874

<https://www.phoenixcontact.com/us/products/1149874>

Material Plug contact coating (intermediate layer)	Ni (1.27 µm/50 µ")
--	--------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 750 (IEC 60603-7)
Insertion force	< 20 N (IEC 60603-7)
Withdrawal force	< 20 N (IEC 60603-7)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection (plugged in)	IP20 (IEC 60603-7)
Degree of protection (Not plugged in)	IP20 (IEC 60603-7)

Test specification for vibration - sine

Acceleration	50 m/s ²
Amplitude	0.35 mm
Sweep speed	1 octave/min

Mounting

Processing notes

Mounting type	SMT
Moisture Sensitive Level	MSL 1 (IEC 60068-2-58)
Solder cycles in the reflow	3 (IEC 60068-2-58)

1149874

<https://www.phoenixcontact.com/us/products/1149874>

Drawings

Diagram



Classification reflow soldering profile

CUC-SP-J1ST-A/R4LB-SMD - Modular RJ45 PCB connectors



1149874

<https://www.phoenixcontact.com/us/products/1149874>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1149874>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

CUC-SP-J1ST-A/R4LB-SMD - Modular RJ45 PCB connectors



1149874

<https://www.phoenixcontact.com/us/products/1149874>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 10.0	EC002637
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-SP-J1ST-A/R4LB-SMD - Modular RJ45 PCB connectors



1149874

<https://www.phoenixcontact.com/us/products/1149874>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com