

SACC-MCI-MST-4CON/1,0 SCO - Contact carrier



1162530

<https://www.phoenixcontact.com/us/products/1162530>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 4-position, Pin, straight-SPEEDCON, T-coding, Individual wires, cable length: 0.5 m, 1.31 mm², UL/cUL stranded hook-up wire

Your advantages

- For compact devices: transmit high power in a confined space
- Convenient field assembly: device connectors for fast on-site mounting
- Customer-specific assemblies and litz wire lengths available
- Standard pin assignments for signal and power transmission with a uniform design-in design

Commercial data

Item number	1162530
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB24
Product key	ABQCEI
GTIN	4063151172565
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	58.772 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Sensor type	Power
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	T

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	63 V
Rated surge voltage	1.5 kV
Rated surge voltage	6 kV AC
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U_N	63 V
Nominal current I_N	12 A
Test voltage	1.5 kV

Connection data

Connection method	Individual wires
-------------------	------------------

Interfaces

Signal type/category	Power
----------------------	-------

Signaling

Status display	no
Status display present	no

Material specifications

Material Contact carrier	PA 6
Material Contact	CuZn
Material Contact surface	Au

SACC-MCI-MST-4CON/1,0 SCO - Contact carrier



1162530

<https://www.phoenixcontact.com/us/products/1162530>

Flammability rating according to UL 94	V0
Conductor material	Bare Cu litz wires

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head locking type	SPEEDCON
Coding	T

Cable/line

Cable length	0.5 m
Cable type	UL/cUL stranded hook-up wire
Signal type/category	Power
Wire diameter incl. insulation	2 mm
Single wire, color	black, brown, blue, white
Cable cross section	1.31 mm ²
Conductor material	Bare Cu litz wires
AWG signal line	16
Material wire insulation	mPPE
Halogen-free	yes
Flame resistance	in acc. to UL 1581 VW1
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation) -20 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
Ambient temperature (operation) (Cable, flexible installation)	-20 °C ... 105 °C (Cable, flexible installation)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 105 °C (cable, fixed installation)

Standards and regulations


Flame resistance	in acc. to UL 1581 VW1
Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111

1162530

<https://www.phoenixcontact.com/us/products/1162530>


Drawings

Schematic diagram



Pin assignment for M12 plug, 4-pos., T-coded, view of plug side

Circuit diagram



Contact assignment of the M12 plug

1162530

<https://www.phoenixcontact.com/us/products/1162530>

Classifications

ECLASS

ECLASS-13.0

27440223

ETIM

ETIM 9.0

EC002635

UNSPSC

UNSPSC 21.0

39121400

1162530

<https://www.phoenixcontact.com/us/products/1162530>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	308c6d0a-85c6-4418-9dd0-f6390dd18731

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com