

# SACC-MCI-MST-4CON/1,5 SCO - Contact carrier



1162531

<https://www.phoenixcontact.com/us/products/1162531>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 4-position, Pin, straight-SPEEDCON, T-coding, Individual wires, cable length: 0.5 m, 1.31 mm<sup>2</sup>, UL/cUL stranded hook-up wire

## Your advantages

- For compact devices: transmit high power in a confined space
- Convenient field assembly: device connectors for fast on-site mounting
- Customer-specific assemblies and litz wire lengths available
- Standard pin assignments for signal and power transmission with a uniform design-in design

## Commercial data

Item number	1162531
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB24
Product key	ABQCEI
GTIN	4063151172961
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	86.242 g
Customs tariff number	85444290
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	T

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated voltage in acc. with IEC 61076-2-101	63 V
Rated surge voltage	1.5 kV
Rated surge voltage	6 kV AC
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage $U_N$	63 V
Nominal current $I_N$	12 A
Test voltage	1.5 kV

### Connection data

Connection method	Individual wires
-------------------	------------------

### Interfaces

Signal type/category	Power
----------------------	-------

### Signaling

Status display	no
Status display present	no

### Material specifications

Material Contact carrier	PA 6
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	V0

# SACC-MCI-MST-4CON/1,5 SCO - Contact carrier



1162531

<https://www.phoenixcontact.com/us/products/1162531>

Conductor material	Bare Cu litz wires
--------------------	--------------------

## Connector

### Connection 1

Head design	Pin
Head cable outlet	straight
Head locking type	SPEEDCON
Coding	T

## Cable/line

Cable length	0.5 m
Cable type	UL/cUL stranded hook-up wire
Signal type/category	Power
Wire diameter incl. insulation	2 mm
Single wire, color	black, brown, blue, white
Cable cross section	1.31 mm <sup>2</sup>
Conductor material	Bare Cu litz wires
AWG signal line	16
Material wire insulation	mPPE
Halogen-free	yes
Flame resistance	in acc. to UL 1581 VW1
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation) -20 °C ... 105 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
Ambient temperature (operation) (Cable, flexible installation)	-20 °C ... 105 °C (Cable, flexible installation)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 105 °C (cable, fixed installation)

## Standards and regulations


Flame resistance	in acc. to UL 1581 VW1
Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111

1162531

<https://www.phoenixcontact.com/us/products/1162531>


## Drawings

Schematic diagram



Pin assignment for M12 plug, 4-pos., T-coded, view of plug side

Circuit diagram



Contact assignment of the M12 plug

# SACC-MCI-MST-4CON/1,5 SCO - Contact carrier



1162531

<https://www.phoenixcontact.com/us/products/1162531>

## Classifications

### ECLASS

ECLASS-13.0

27440223

### ETIM

ETIM 9.0

EC002635

### UNSPSC

UNSPSC 21.0

39121400

1162531

<https://www.phoenixcontact.com/us/products/1162531>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b2c747a4-83c3-4beb-9a71-0d26b020a065

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)