# CUC-SP-J1ST-A/R4LT-SMD-LED - Modular RJ45 PCB connectors

1149873

https://www.phoenixcontact.com/us/products/1149873

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 90 °, Tab up, Shielded, LED (green, yellow), number of positions: 8, PoE++, SMT, SMD, Reflow, IP20, type of packaging: Tape and Reel

## Your advantages

- The reflow capability enables efficient, cost-optimized processing
- Tape-on-reel packaging is perfect for automated processing
- The extended temperature range from -40 °C to +85 °C enables use in demanding applications

## Commercial data

| | |
|---|---|
| Item number | 1149873 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | AB12 |
| Product key | ABNADB |
| GTIN | 4063151145569 |
| Weight per piece (including packing) | 7.389 g |
| Weight per piece (excluding packing) | 6.016 g |
| Customs tariff number | 85366930 |
| Country of origin | TW |

## Technical data

### Product properties

| | |
|---|---|
| Slots | 1x1 single-port |
| Orientation to PCB | 90.00 ° |
| Type | SMD |
| Connection profile | RJ45 |
| Number of positions | 8 (8P8C) |
| Type of locking | Snap-in locking, Tab up |
| Shielding | Shielded |
| Status display | LED (green, yellow) |
| Processing notes | Reflow |
| Type of packaging | Tape and Reel |
| Power transmission | PoE++ (according to IEEE 802.3bt) |
| Power PSE | 90 W (Class 8 in accordance with IEEE 802.3bt) |
| Power PD | 71 W (Class 4 in accordance with IEEE 802.3bt) |

### Electrical properties

| | |
|---|---|
| Pollution degree | 2 (IEC 60664-1) |
| Overvoltage category | I (IEC 60664-1) |
| Rated voltage | 72 V DC |
| Rated surge voltage | 1.5 kV DC (IEC 60664-1) |
| Rated current | 1.5 A (IEC 60603-7) |
| Insulation resistance | > 500 MΩ (IEC 60603-7) |
| Test voltage (Contact/contact) | 1.5 kV DC (IEC 60603-7) |
| Test voltage (Contact/shield) | 1.5 kV DC (IEC 60603-7) |

### Dimensions

| | |
|---|---|
| Length | 15.75 mm |
| Width | 18.8 mm |
| Height | 14.8 mm |
| Installed height | 13.50 mm |

### Material specifications

| | |
|---|---|
| Material Contact carrier | PA |
| Flame resistance | UL 94 V0 |
| Halogen-free | no |
| Material Housing | Copper alloy |
| Material Housing coating | Ni (0,508 µm / 20 µ") |
| Material Housing pin coating (top layer/selective) | Ni (0,508 µm / 20 µ") |
| Material Contact | Phosphor bronze |
| Material Solder contact coating (intermediate layer) | Ni (1.27 µm/50 µ") |

| | |
|---|---|
| Material Solder contact coating (top layer/selective) | Au (Flash) |
| Material Plug contact coating (top layer/selective) | Au (0,152 µm / 6 µ") |
| Material Plug contact coating (intermediate layer) | Ni (1.27 µm/50 µ") |

## Mechanical properties

Mechanical data

| | |
|---|---|
| Insertion/withdrawal cycles | > 750 (IEC 60603-7) |
| Insertion force | < 20 N (IEC 60603-7) |
| Withdrawal force | < 20 N (IEC 60603-7) |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Degree of protection (plugged in) | IP20 (IEC 60603-7) |
| Degree of protection (Not plugged in) | IP20 (IEC 60603-7) |

Test specification for vibration - sine

| | |
|---|---|
| Acceleration | 50 m/s² |
| Amplitude | 0.35 mm |
| Sweep speed | 1 octave/min |


## Mounting

Processing notes

| | |
|---|---|
| Mounting type | SMT |
| Moisture Sensitive Level | MSL 1 (IEC 60068-2-58) |
| Solder cycles in the reflow | 3 (IEC 60068-2-58) |

## Drawings

Diagram




Classification reflow soldering profile

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1149873

**cUL Recognized**
Approval ID: FILE E 335024

**UL Recognized**
Approval ID: FILE E 335024

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002637 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.245 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com