

SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting



1163114

<https://www.phoenixcontact.com/us/products/1163114>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Power, 5-position, Socket, straight, M12, L-coding, on free cable end, Individual wires, cable length: 1.5 m, 2.50 mm², PEX litz wire, potted, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- For compact devices: transmit high power in a confined space
- Easy-to-install, optimized XL housing contour with wrench size 19
- Mechanical tightening limitation for long-term-stable gasket
- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- For high transmission safety: shield connection to the housing with optional EMC nut

Commercial data

Item number	1163114
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB24
Product key	ABQCHB
GTIN	4063151174811
Weight per piece (including packing)	235.8 g
Weight per piece (excluding packing)	233.527 g
Customs tariff number	85444290
Country of origin	DE

SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting



1163114

<https://www.phoenixcontact.com/us/products/1163114>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Notes on operation	FE not connected to metal parts that can be touched, no protective function
Order information:	Lock nut is included in the scope of delivery
General	Contact connection method: Crimp connection

Mounting

Mounting type	Rear mounting (M16 x 1.5, XL version, with flat nut, tightening limitation)
Tightening torque	1.5 Nm ... 2 Nm

Product properties

Product type	Circular connectors (device side)
Application	Power
Number of positions	5
Connection profile	4+FE
No. of cable outlets	1
Shielded	no
Coding	L
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Molding compound	PUR (potted)
Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	63 V
--	------

SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting



1163114

<https://www.phoenixcontact.com/us/products/1163114>

Rated surge voltage	1.5 kV
Rated surge voltage	1.5 kV AC/DC
Nominal voltage U_N	63 V DC
Nominal current I_N	16 A
Test voltage	1.5 kV
Test voltage Core/Core	6 kV

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Socket
Conductor cross-section	2.5 mm ²
Tightening torque	1.5 Nm ... 2 Nm

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	L

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	1.5 m
Cable type	PEX litz wire
Signal type/category	Power
Single wire, color	brown 1, white 2, blue 3, black 4, gray FE
Cable cross section	2.5 mm ²
AWG signal line	14
Test voltage Core/Core	6 kV
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation) -25 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting



1163114

<https://www.phoenixcontact.com/us/products/1163114>

	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation)
Ambient temperature (operation) (Cable, flexible installation)	-25 °C ... 105 °C (Cable, flexible installation)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 105 °C (cable, fixed installation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111


SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting

1163114

<https://www.phoenixcontact.com/us/products/1163114>

Drawings

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting



1163114

<https://www.phoenixcontact.com/us/products/1163114>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1163114>

 cULus Recognized Approval ID: E468743-20180113		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine					
		63 V	16 A	14	-

SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting



1163114

<https://www.phoenixcontact.com/us/products/1163114>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 10.0	EC003570
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M12FSL-4FE-M16XL/1,5 - Device connector rear mounting



1163114

<https://www.phoenixcontact.com/us/products/1163114>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a56ea545-2f80-4e4a-b2f3-b1c7ec7fc7c1

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com