# SD FLASH 8GB PLCNEXT MEMORY LIC - Program/configuration memory

1151112

https://www.phoenixcontact.com/us/products/1151112

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.




Program and configuration memory for storing the application programs, licenses, and other files in the file system of the PLC, plug-in, 8 GB.

## Your advantages

- For storing application programs, the licenses, and other files in the file system of the PLC
- Program and configuration memory

ELEKTROGERÄTE RÜCKNAHME

## Commercial data

| | |
|---|---|
| Item number | 1151112 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DR09 |
| Product key | DRADZA |
| GTIN | 4063151149031 |
| Weight per piece (including packing) | 9.5 g |
| Weight per piece (excluding packing) | 9 g |
| Customs tariff number | 85235190 |
| Country of origin | DE |

## Technical data

### Notes

Note on application

| | |
|---|---|
| Note on application | Only for industrial use |

### Product properties

| | |
|---|---|
| Product type | Storage medium |
| Application | Program/configuration memory |
| Mounting position | vertical |
| Memory type | FLASH-EPROM |
| Memory size | 8 GByte |
| Partitioning (License container) | 64 Mbyte (prepartitioned) |
| Partitioning (Superimposed file system) | 7.5 GByte (prepartitioned) |

### Electrical properties

| | |
|---|---|
| Maximum power dissipation for nominal condition | 0.264 W |

Supply

| | |
|---|---|
| Supply voltage | 3.3 V DC |
| Supply voltage range | 2.7 V DC ... 3.6 V DC |
| Typical current consumption | typ. 80 mA |

### Material specifications

| | |
|---|---|
| Material (Housing) | Plastic |
| Housing material | Plastic |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 85 °C |

### Mounting

| | |
|---|---|
| Mounting position | vertical |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27242212 |
| ECLASS-15.0 | 27242212 |

### ETIM

| | |
|---|---|
| ETIM 9.0 | EC000192 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 32101600 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com