

# SPE-T1-STRM-90 - SPE PCB connector



1163797

<https://www.phoenixcontact.com/us/products/1163797>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SPE PCB connector, design: IEC 63171-2, degree of protection: IP20, number of positions: 2, 1 Gbps, CAT B (ISO/IEC 63171), material: Metal, connection method: THR solder connection, cable outlet: straight, Single Pair Ethernet

## Your advantages

- Compact design for maximum space savings
- Connectors in accordance with IEC 63171-2
- THR solderable
- Robust industrial design
- 360° shielding
- Data transmission up to 600 MHz

## Commercial data

Item number	1163797
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB13
Product key	ABNBDA
GTIN	4063151175979
Weight per piece (including packing)	4.14 g
Weight per piece (excluding packing)	3.96 g
Customs tariff number	85366930
Country of origin	DE

# SPE-T1-STRM-90 - SPE PCB connector



1163797

<https://www.phoenixcontact.com/us/products/1163797>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	SPE
Sensor type	Single Pair Ethernet
Number of positions	2
Connection profile	SPE
Type of packaging	Tape and Reel
Pitch	7.62 mm
Number of slots	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	II
Degree of pollution	2

### Electrical properties

Rated voltage (III/2)	72 V DC
Rated surge voltage	2250 V DC
Rated surge voltage (III/2)	1500 V
Rated current	4 A
Frequency range	600 MHz
Insulation resistance	> 1 TΩ
Transmission medium	Copper
Transmission speed	1 Gbps (in accordance with IEEE 802.3 bp) 100 Mbps (in accordance with IEEE 802.3 bw) 10 Mbps (in accordance with IEEE 802.3 cg)
Transmission characteristics (category)	CAT B (IEC 63171)
Transmission speed	1 Gbps
Power transmission	PoDL

### Connection data

#### Connection technology

Connection method	THR solder connection
-------------------	-----------------------

### Dimensions

Width	5 mm
Height	8.35 mm
Length	14.2 mm

### Material specifications

Flammability rating according to UL 94	V0
--	----

# SPE-T1-STRM-90 - SPE PCB connector



1163797

<https://www.phoenixcontact.com/us/products/1163797>

Housing material	Metal
Contact material	Copper alloy
Contact surface material	Ni/Au
Contact carrier material	LCP

## Cable/line

Test voltage Core/Core	1000 V DC
Test voltage Core/Shield	2250.00 V DC
Halogen-free	yes
Resistance to oil	yes
Flame resistance	UL 94 V0

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 750
Insertion force per signal contact	< 1.50 N
Extraction force per signal contact	< 1.5 N

## Standards and regulations

Flame resistance	UL 94 V0
Resistance to oil	yes

## Mounting


Mounting type	THR soldering
---------------	---------------

### Processing notes

Moisture Sensitive Level	MSL 1
--------------------------	-------

Drawings

Diagram



Classification reflow soldering profile

# SPE-T1-STRM-90 - SPE PCB connector




1163797

<https://www.phoenixcontact.com/us/products/1163797>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1163797>

 <b>cULus Recognized</b> Approval ID: E335024-20220331		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine		60 V	1.4 A	-	-

# SPE-T1-STRM-90 - SPE PCB connector



1163797

<https://www.phoenixcontact.com/us/products/1163797>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SPE-T1-STRM-90 - SPE PCB connector



1163797

<https://www.phoenixcontact.com/us/products/1163797>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)