

LS-EMLP (180X180)/AC RD-WH - Device marker




1166273

<https://www.phoenixcontact.com/us/products/1166273>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Sheet, red (RAL 3001), unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 1, text field height: 180 mm, text field width: 180 mm



Your advantages

- Stick-on device marking
- Individually configurable equipment marking in proven laser sheet format for optimum positioning in the marking device
- Very high contrast due to the red top layer with white marking

Commercial data

Item number	1166273
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG19
Product key	BG241D
GTIN	4063151179854
Weight per piece (including packing)	43.1 g
Weight per piece (excluding packing)	43 g
Customs tariff number	39205100
Country of origin	DE

LS-EMLP (180X180)/AC RD-WH - Device marker



1166273

<https://www.phoenixcontact.com/us/products/1166273>

Technical data

Notes

Material information	The white base material (PMMA) cannot be cut/assembled with the TOPMARK LASER or the TOPMARK NEO.
----------------------	---

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	1
Identification technology	Direct laser marking

Dimensions

Width	180 mm
Height	180 mm
Depth	0.85 mm

Text field

Text field width	180 mm
Text field height	180 mm

Material specifications

Adhesive	Acrylic
Color	red (RAL 3001)
Material	Modified acrylic + hot-stamp foil
Base element material	Modified acrylic + hot-stamp foil
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
---------------	--------------------------------

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

LS-EMLP (180X180)/AC RD-WH - Device marker



1166273

<https://www.phoenixcontact.com/us/products/1166273>

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	70 °C

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

LS-EMLP (180X180)/AC RD-WH - Device marker



1166273

<https://www.phoenixcontact.com/us/products/1166273>

Test duration	96 h
---------------	------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

LS-EMLP (180X180)/AC RD-WH - Device marker



1166273

<https://www.phoenixcontact.com/us/products/1166273>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-EMLP (180X180)/AC RD-WH - Device marker



1166273

<https://www.phoenixcontact.com/us/products/1166273>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com