

# AXL F BK EIP XC - Bus coupler

1167192

<https://www.phoenixcontact.com/us/products/1167192>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Bus coupler, EtherNet/IP™, RJ45 jack, Extreme conditions version, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connector

## Product description

The bus coupler is intended for use within an EtherNet/IP™ network. It is the link to the Axioline F I/O system. Up to 63 Axioline F devices can be connected to the bus coupler. A corresponding EDS file is available for integrating the Axioline F station into the programming system. This file can be downloaded at: [www.phoenixcontact.com/product/1167192](http://www.phoenixcontact.com/product/1167192)

## Your advantages

- 2 Ethernet ports (with integrated switch)
- Transmission speed of 10 Mbps and 100 Mbps
- Rotary coding switches for setting the IP address assignment and other functions
- Firmware can be updated
- Runtime in bus coupler is negligible (almost 0 μs)
- Typical cycle time of the Axioline F local bus is around 10 μs
- Web-based management
- Supports the operation of Axioline Smart Elements
- Supports passive Smart Elements (firmware version 1.30 or later)
- Supports IOL-CONF (firmware version 1.30 and later)
- Supports Diag+
- Can be used under extreme ambient conditions
- Extended temperature range of -40 °C ... +70 °C (see "Tested successfully: use under extreme ambient conditions" in the data sheet)
- Partially coated PCBs

# AXL F BK EIP XC - Bus coupler



1167192

<https://www.phoenixcontact.com/us/products/1167192>

## Commercial data

Item number	1167192
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR02
Product key	DRI21D
GTIN	4063151184674
Weight per piece (including packing)	218 g
Weight per piece (excluding packing)	218 g
Customs tariff number	85176200
Country of origin	DE

# AXL F BK EIP XC - Bus coupler




1167192

<https://www.phoenixcontact.com/us/products/1167192>

## Technical data

### Dimensions

Dimensional drawing	
Width	45 mm
Height	126.1 mm
Depth	74 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

### Notes

Note on application	
Note on application	Only for industrial use

### Material specifications

Color (Housing)	gray (RAL 7042)
-----------------	-----------------

### Interfaces

Supported protocols	EtherNet/IP™
	SNMP
	HTTP
	TFTP
	FTP
	BootP
	DHCP
	DCP
DLR	

#### EtherNet/IP™

Number of interfaces	2
Connection method	RJ45 jack
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps (Half or full duplex mode (automatic detection, can be adjusted manually))
Transmission physics	Ethernet in RJ45 twisted pair

#### Axioline F local bus

Number of interfaces	1
Connection method	Bus base module

# AXL F BK EIP XC - Bus coupler



1167192

<https://www.phoenixcontact.com/us/products/1167192>

Transmission speed	100 Mbps
Service	
Number of interfaces	1
Connection method	USB type C

## System properties

### System limits

Amount of process data (Input data)	max. 504 Byte
Amount of process data (Output data)	max. 504 Byte
Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 63

### Programming data

Register length (master)	1484 Byte
--------------------------	-----------

## Product properties

Product type	I/O component
Product family	Axioline F
Type	block modular
Mounting position	any (observe temperature derating)
Scope of supply	including bus base module and Axioline F connector
Special properties	Extreme conditions version

### Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

## Electrical properties

Maximum power dissipation for nominal condition	4 W
---	-----

Potentials: Communications power  $U_L$  feed-in (the supply of the Axioline F local bus  $U_{BUS}$  is generated from  $U_L$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 583 mA (2.0 A at $U_{BUS}$ , $U_L = 24$ V, applications with UL approval, use in zone 2 potentially explosive area)
	max. 670 mA (2.5 A on $U_{BUS}$ , $U_L = 24$ V)
Current consumption	typ. 85 mA (without I/O modules, $U_L = 24$ V)
Protective circuit	Surge protection; electronic
	Reverse polarity protection; electronic

Potentials: Axioline F local bus supply ( $U_{BUS}$ )

Supply voltage	5 V DC (via bus base module)
Power supply unit	max. 2.5 A
	max. 2 A (Applications with UL approval, use in zone 2 potentially explosive area)

## Electrical isolation/isolation of the voltage ranges

Test voltage: Ethernet interface 1 / Ethernet interface 2	1500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 1 / 24 V communications voltage (U <sub>L</sub> ) feed-in	1500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 2 / 24 V communications voltage (U <sub>L</sub> ) feed-in	1500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 1 / functional ground	1500 V AC, 50 Hz, 1 min
Test voltage: Ethernet interface 2 / functional ground	1500 V AC, 50 Hz, 1 min
Test voltage: 24 V communications voltage (U <sub>L</sub> ) feed-in / functional ground	500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Axioline F connector
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual.

### Axioline F connector

Connection method	Push-in connection
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual.
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C (Standard, applications with UL approval, use in zone 2 potentially explosive area; mounting position: panel mounting on horizontal DIN rail)
	-25 °C ... 55 °C (Standard, applications with UL approval, use in zone 2 potentially explosive area; mounting position: any)
	-40 °C ... 70 °C (Extended, see section "Tested successfully: use under extreme ambient conditions" in the data sheet.)
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

### Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	30g




# AXL F BK EIP XC - Bus coupler

1167192


<https://www.phoenixcontact.com/us/products/1167192>

## Drawings

Dimensional drawing



Connection diagram




# AXL F BK EIP XC - Bus coupler

1167192

<https://www.phoenixcontact.com/us/products/1167192>

Block diagram



Internal wiring of the terminal points

# AXL F BK EIP XC - Bus coupler



1167192

<https://www.phoenixcontact.com/us/products/1167192>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1167192>



**cULus Listed**

Approval ID: E238705



**IECEX**

Approval ID: IECEX ULD 20.0026X



**ATEX**

Approval ID: UL 20 ATEX 2441X



**cULus Listed**

Approval ID: E366272



**CCC**

Approval ID: 2021122309114456\_CN

# AXL F BK EIP XC - Bus coupler



1167192

<https://www.phoenixcontact.com/us/products/1167192>

## Classifications

### ECLASS

ECLASS-13.0	27242608
ECLASS-15.0	27242608

### ETIM

ETIM 10.0	EC001604
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# AXL F BK EIP XC - Bus coupler



1167192

<https://www.phoenixcontact.com/us/products/1167192>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	4,4'-isopropylidenediphenol(CAS: 80-05-7)
	Lead(CAS: 7439-92-1)
SCIP	c356d99b-0801-4f28-8f57-8c182e20c664

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)