

# ES-BBC-5-3 BK - Connector

1155599

<https://www.phoenixcontact.com/us/products/1155599>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a 3-position version

Connector, Range of articles: BBC, design: Connector, color: black, number of positions: 1, rated voltage: 1500 V DC, rated current: 120 A, Connection method: Spring-cage connection

## Your advantages

- Quick installation: direct contacting of battery modules on the busbar in the rack
- Safe installation: touch-protected battery terminals even when not plugged in
- Diverse areas of application: modular design allows different currents
- Slide-in system with integrated interface: no wiring effort during installation

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1155599       |
| Packing unit                         | 6 pc          |
| Minimum order quantity               | 6 pc          |
| Sales key                            | AB04          |
| Product key                          | ABLDAD        |
| GTIN                                 | 4063151157609 |
| Weight per piece (including packing) | 141.8 g       |
| Weight per piece (excluding packing) | 114.178 g     |
| Customs tariff number                | 85359000      |
| Country of origin                    | CN            |

## Technical data

### Notes

#### Safety note

|             |   |
|-------------|---|
| Safety note | <ul style="list-style-type: none"> <li>• <b>WARNING:</b> Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.</li> </ul>  |
|             | <ul style="list-style-type: none"> <li>• <b>WARNING:</b> Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li> </ul> |
|             | <p><b>WARNING:</b> The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p>  |
|             | <ul style="list-style-type: none"> <li>• Assembled products may not be manipulated or improperly opened.</li> </ul>   |
|             | <ul style="list-style-type: none"> <li>• Observe the corresponding technical data. You will find information:                             <ul style="list-style-type: none"> <li>o On the product</li> <li>o On the packing label</li> <li>o In the supplied documentation</li> <li>o Online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> under the product</li> </ul> </li> </ul>  |
|             | <ul style="list-style-type: none"> <li>• The installation notes/Design In documents online on the download page at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> must be observed for this product.</li> </ul>  |
|             | <ul style="list-style-type: none"> <li>• Operate the connector only when it is fully plugged in.</li> <li>• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).</li> </ul>   |

### Product properties

|                     |                               |
|---------------------|-------------------------------|
| Product type        | Connectors for energy storage |
| Product family      | BBC                           |
| Type                | Connector                     |
| Number of positions | 1                             |
| Number of slots     | 1                             |

#### Insulation characteristics

|                     |   |
|---------------------|---|
| Degree of pollution | 3 |
|---------------------|---|

### Electrical properties

|                             |           |
|-----------------------------|-----------|
| Rated voltage (III/3)       | 1500 V    |
| Rated voltage               | 1500 V DC |
| Rated surge voltage         | 12 kV     |
| Rated surge voltage (III/3) | 12 kV     |

# ES-BBC-5-3 BK - Connector



1155599

<https://www.phoenixcontact.com/us/products/1155599>

|                       |        |
|-----------------------|--------|
| Rated current         | 120 A  |
| Insulation resistance | ≥ 5 MΩ |

## Connection data

|                   |                        |
|-------------------|------------------------|
| Connection method | Spring-cage connection |
|-------------------|------------------------|

## Dimensions

|        |         |
|--------|---------|
| Width  | 41 mm   |
| Height | 43.9 mm |
| Length | 118 mm  |

## Material specifications

|  |        |
|--|--------|
| Color                                  | black  |
| Color of the housing part              | black  |
| Material Housing                       | PA 6.6 |
| Material Contact                       | Copper |
| Flammability rating according to UL 94 | V0     |
| Insulating material group              | I      |
| Contact surface material               | Ni/Sn  |

## Cable/line

|              |     |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

## Mechanical properties

### Mechanical data

|                             |         |
|-----------------------------|---------|
| Insertion/withdrawal cycles | ≥ 25    |
| Insertion force             | ≤ 120 N |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                       |
|---------------------------------|-----------------------|
| Degree of protection            | IP20 (Not plugged in) |
| Ambient temperature (operation) | -10 °C ... 50 °C      |
| Altitude                        | ≤ 2000 m              |

## Mounting

|               |   |
|---------------|---|
| Assembly note | Use busbars that are 4 mm thick with rounded edges in accordance with DIN EN 13601. The busbars must be coated (tin-plated, thickness: 8 μm ... 30 μm). |
|---------------|---|

# ES-BBC-5-3 BK - Connector



1155599

<https://www.phoenixcontact.com/us/products/1155599>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27440312 |
| ECLASS-13.0 | 27440312 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002641 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# ES-BBC-5-3 BK - Connector



1155599

<https://www.phoenixcontact.com/us/products/1155599>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)