

ES-BBC-5-4 BK - Connector

1155600

<https://www.phoenixcontact.com/us/products/1155600>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a 3-position version

Connector, Range of articles: BBC, design: Connector, color: black, number of positions: 1, rated voltage: 1500 V DC, rated current: 160 A, Connection method: Spring-cage connection

Your advantages

- Quick installation: direct contacting of battery modules on the busbar in the rack
- Safe installation: touch-protected battery terminals even when not plugged in
- Diverse areas of application: modular design allows different currents
- Slide-in system with integrated interface: no wiring effort during installation

Commercial data

Item number	1155600
Packing unit	4 pc
Minimum order quantity	4 pc
Sales key	AB04
Product key	ABLDAD
GTIN	4063151156855
Weight per piece (including packing)	190 g
Weight per piece (excluding packing)	148.737 g
Customs tariff number	85359000
Country of origin	CN

Technical data

Notes

Safety note

Safety note	<ul style="list-style-type: none"> • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
	<ul style="list-style-type: none"> • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p>
	<ul style="list-style-type: none"> • Assembled products may not be manipulated or improperly opened.
	<ul style="list-style-type: none"> • Observe the corresponding technical data. You will find information: <ul style="list-style-type: none"> o On the product o On the packing label o In the supplied documentation o Online at phoenixcontact.com/products under the product
	<ul style="list-style-type: none"> • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.
	<ul style="list-style-type: none"> • Operate the connector only when it is fully plugged in. • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Connectors for energy storage
Product family	BBC
Type	Connector
Number of positions	1
Number of slots	1

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Rated voltage (III/3)	1500 V
Rated voltage	1500 V DC
Rated surge voltage	12 kV
Rated surge voltage (III/3)	12 kV

ES-BBC-5-4 BK - Connector



1155600

<https://www.phoenixcontact.com/us/products/1155600>

Rated current	160 A
Insulation resistance	≥ 5 MΩ

Connection data

Connection method	Spring-cage connection
-------------------	------------------------

Dimensions

Width	41 mm
Height	56.4 mm
Length	118 mm

Material specifications

Color	black
Color of the housing part	black
Material Housing	PA 6.6
Material Contact	Copper
Flammability rating according to UL 94	V0
Insulating material group	I
Contact surface material	Ni/Sn

Cable/line

Halogen-free	yes
--------------	-----

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 25
Insertion force	≤ 120 N

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (Not plugged in)
Ambient temperature (operation)	-10 °C ... 50 °C
Altitude	≤ 2000 m

Mounting

Assembly note	Use busbars that are 4 mm thick with rounded edges in accordance with DIN EN 13601. The busbars must be coated (tin-plated, thickness: 8 μm ... 30 μm).
---------------	---

ES-BBC-5-4 BK - Connector



1155600

<https://www.phoenixcontact.com/us/products/1155600>

Classifications

ECLASS

ECLASS-15.0	27440312
ECLASS-13.0	27440312

ETIM

ETIM 10.0	EC002641
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ES-BBC-5-4 BK - Connector



1155600

<https://www.phoenixcontact.com/us/products/1155600>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com