

SACB-4/ 8-C QO - Distributor box



1156003

<https://www.phoenixcontact.com/us/products/1156003>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, connection method: QUICKON, 0.14 mm² ... 0.5 mm², number of slots: 4, number of positions: 5, slot assignment: Double, status display: no, Universal; master cable connection: Pluggable screw connection 180°, shielding: no, When connecting 5 conductors, max. 0.5 mm² can be connected

Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Convenient: increased machine availability thanks to quick and easy diagnostics
- Innovative and time-saving assembly with insulation displacement connection
- Flexible: distributor box with connector hood for on-site assembly

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1156003 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF41 |
| Product key | AF3DBD |
| GTIN | 4063151158521 |
| Weight per piece (including packing) | 267.8 g |
| Weight per piece (excluding packing) | 267 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACB-4/ 8-C QO - Distributor box



1156003

<https://www.phoenixcontact.com/us/products/1156003>

Technical data

Notes

| | |
|---------------------|---|
| Assembly note | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
| Note on application | Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories". |
| Note on application | Cables with 5 conductors may have a maximum connection cross-section of 0.5 mm ² /20 AWG. |

Product properties

| | |
|---------------------|-----------------|
| Product type | Distributor box |
| Number of positions | 5 |
| Number of slots | 4 |
| LED | no |

Electrical properties

| | |
|---|---------|
| Nominal voltage U _N | 48 V AC |
| | 60 V DC |
| Rated current, total | 10 A |
| Max. current carrying capacity per path | 2 A |
| Current carrying capacity per slot | 4 A |

Connection data

Conductor connection

| | |
|--|--|
| Sensor/actuator connection system | QUICKON |
| Conductor cross-section Flexible signal line | 0.14 mm ² ... 0.5 mm ² |
| Conductor cross-section Flexible power supply | 0.14 mm ² ... 0.5 mm ² |
| Connection cross section AWG Flexible signal line | 26 ... 20 |
| Connection cross section AWG Flexible power supply | 26 ... 20 |
| Stripping length Signal line | 7 mm |
| Stripping length of the sheath | 50 mm (Master cable) |
| Tightening torque, cover screw | 0.35 Nm |
| Tightening torque of mounting screw for fixing the housing | 0.5 Nm |
| Tightening torque, union nut | 4 Nm |

Connection assignment

| | |
|--|-------------------|
| Slot/position = Wire color or connection | 1 / 4 (A) = 1 / 4 |
| | 1 / 2 (B) = 1 / 2 |
| | 2 / 4 (A) = 2 / 4 |
| | 2 / 2 (B) = 2 / 2 |
| | 3 / 4 (A) = 3 / 4 |
| | 3 / 2 (B) = 3 / 2 |

SACB-4/ 8-C QO - Distributor box

1156003


<https://www.phoenixcontact.com/us/products/1156003>

| | |
|--|-----------------------------------|
| | 4 / 4 (A) = 4 / 4 |
| | 4 / 2 (B) = 4 / 2 |
| | 1-4 / 1 (+ 48 V) = U _N |
| | 1-4 / 3 (0 V) = 0 V |
| | 1-4 / 5 (PE) = PE |

Signaling

| | |
|------------------------|----|
| Status display present | no |
|------------------------|----|

Dimensions

| | |
|------------------------|---|
| Dimensional drawing |  |
| Width | 58 mm |
| Height | 45 mm |
| Length | 131 mm |
| Wrench size, union nut | 16 mm |

Material specifications

| | |
|--|------------------------|
| Material Housing | PBT |
| Material Molding compound | PUR |
| Flammability rating according to UL 94 | V0 |
| Seal material O-ring | FKM |
| Seal material | FKM |
| Contact material | Steel/copper |
| Contact surface material | Sn |
| Contact carrier material | PA 6.6 |
| Material of contact, master cable side | CU alloy |
| Material of the contact carrier on the master cable side | PA 6.6 V0 |
| Material of contact surface, master cable side | Ni |
| Wire insulation material | PVC / PE / PP / rubber |

Cable/line

| | |
|-------------------------|----------------------------|
| External cable diameter | 7 mm ... 12 mm |
| Connection method | Pluggable screw connection |

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|

SACB-4/ 8-C QO - Distributor box



1156003

<https://www.phoenixcontact.com/us/products/1156003>

| | |
|---------------------------------|-----------------------------------|
| Ambient temperature (operation) | -30 °C ... 80 °C |
| | -5 °C ... 50 °C (During assembly) |


SACB-4/ 8-C QO - Distributor box



1156003

<https://www.phoenixcontact.com/us/products/1156003>

Drawings




SACB-4/ 8-C QO - Distributor box

1156003

<https://www.phoenixcontact.com/us/products/1156003>

Functional drawing



Schematic diagram



QUICKON connection, 5-pos.

SACB-4/ 8-C QO - Distributor box



1156003

<https://www.phoenixcontact.com/us/products/1156003>

Circuit diagram



SACB-4/ 8-C QO - Distributor box



1156003

<https://www.phoenixcontact.com/us/products/1156003>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440111 |
| ECLASS-15.0 | 27440111 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003558 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

SACB-4/ 8-C QO - Distributor box



1156003

<https://www.phoenixcontact.com/us/products/1156003>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 73d4874d-acf7-4f7a-b185-e404568e0e2c |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com