

# CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert



1157964

<https://www.phoenixcontact.com/us/products/1157964>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 male insert, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6<sub>A</sub> (IEC 60512-27-100:2008, TIA-568-C.2:2009), material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: straight, Ethernet

## Your advantages

- Easy and time-saving assembly with IDC fast connection technology
- Can be used internationally due to EAC, UL 1863, and CAN/CSA C22.2
- Ideal companion for servicing or repairs in the field: no special tools required for mounting
- Future-proof due to CAT6<sub>A</sub> with 10 Gbps
- 360° shielding ensures reliable transmission, even in industrial applications

## Commercial data

Item number	1157964
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNAAB
GTIN	4063151163914
Weight per piece (including packing)	21 g
Weight per piece (excluding packing)	11.772 g
Customs tariff number	85366990
Country of origin	PL

# CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert



1157964

<https://www.phoenixcontact.com/us/products/1157964>

## Technical data

### Product properties

Product type	Data connector (cable side)
Series	HC-M-RJ45-AD-I
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight
Positions/contacts	8P8C

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Contact resistance	< 20 mΩ (Contact) < 100 mΩ (shield)
Insulation resistance	> 500 MΩ
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 mΩ (Wire – IDC) 0.005 Ω (Litz wires – IDC)
Transmission speed	10 Gbps
Transmission characteristics (category)	CAT6 <sub>A</sub>
Transmission speed	10 Gbps
Power transmission	PoE++ in accordance with: IEEE 802.3bt
Wave impedance	100 Ω

### Connection data

#### Connection technology

Connection method	Insulation displacement connection
Connection cross section AWG	26 ... 24 (solid) 26 ... 24 (flexible)
Conductor cross-section	0.14 mm <sup>2</sup> ... 0.22 mm <sup>2</sup> (solid) 0.14 mm <sup>2</sup> ... 0.22 mm <sup>2</sup> (flexible)
Connection in acc. with standard	IEC 60603-7-51
Cable outlet, angle	180

# CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert



1157964

<https://www.phoenixcontact.com/us/products/1157964>

## Dimensions

Width	13.6 mm
Height	43.4 mm
Length	10.5 mm

## Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Ni
Contact material	CuSn
Contact surface material	Au/Ni
Material for screw connection	PA

## Cable/line

External cable diameter	5 mm ... 9 mm
External cable diameter	5 mm ... 9 mm
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V
Wave impedance	100 Ω

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

## Environmental and real-life conditions

### Test specification

Type of test	Vibration test
Specification	IEC 60068-2-6
Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s <sup>2</sup>
Test duration	20.00 s

## Mounting

Mounting type	For field assembly
---------------	--------------------

# CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert



1157964

<https://www.phoenixcontact.com/us/products/1157964>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1157964>

 <b>cULus Recognized</b> Approval ID: E335024-20170228				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	56.5 V	1.75 A	-	-

# CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert



1157964

<https://www.phoenixcontact.com/us/products/1157964>

## Classifications

### ECLASS

ECLASS-13.0	27440114
ECLASS-15.0	27440114

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert



1157964

<https://www.phoenixcontact.com/us/products/1157964>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.607 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)