SPE-T1-CCP-SF/3,0/AWG22/CCP-SF - Patch cable

1183810

https://www.phoenixcontact.com/us/products/1183810

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRIMP



Patch cable, Single Pair Ethernet CAT B (1 Gbps), 2-position, Plug straight SPE / IP20, on Plug straight SPE / IP20, cable length: 3 m

Your advantages

- Compact design
- Connectors in accordance with IEC 63171-2
- Mechanical interlock with locking clip
- Robust industrial design
- 360° shielding
- Data transmission up to 600 MHz

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	1183810
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB13
Product key	ABNBCB

GTIN	4063151221348
Weight per piece (including packing)	125.5 g
Weight per piece (excluding packing)	125 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	2
No. of cable outlets	1
Shielded	yes

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Interfaces

Signal type/category	Single Pair Ethernet CAT B, 1 Gbps (in accordance with IEEE 802.3 bp)

Electrical properties

Rated voltage (III/2)	72 V DC
Rated current	4 A
Frequency range	600 MHz
Insulation resistance	> 1 TΩ
Transmission speed	1 Gbps (in accordance with IEEE 802.3 bp)
	100 Mbps (in accordance with IEEE 802.3 bw)
	10 Mbps (in accordance with IEEE 802.3 cg)
Transmission characteristics (category)	CAT B
Power transmission	PoDL
Wave impedance	100 Ω
Max. conductor resistance	59.4 MΩ/km

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000
Insertion force per signal contact	< 10.00 N
Extraction force per signal contact	< 10 N

Material specifications

Material Housing	Plastic
Material Insulating body	LCP
Flammability rating according to UL 94	V0
Housing material	TPU
Contact material	Cu alloy
Contact surface material	Ni/Au
Contact carrier material	LCP
Outer sheath, material	PVC

Conductor material	Cu

Dimensions

Width	8 mm
Height	14 mm
Length	36 mm

Connection data

Connection technology

Connection method	Crimp connection

Conductor connection

Connection method	Crimp connection

Connector

Connection 1

Type	Plug straight SPE / IP20
Number of positions	2
Shielded	yes
Insertion/withdrawal cycles	≥ 1000
Degree of protection	IP20


Connection 2

Type	Plug straight SPE / IP20
Number of positions	2
Shielded	yes
Insertion/withdrawal cycles	≤ 1000
Degree of protection	IP20

Cable/line

Cable length	3 m

Single Pair Ethernet PUR flexible, black [97B]

Dimensional drawing	
UL AWM Style	2095 (80°C/300 V)
Number of positions	2
Shielded	yes
Cable type	Single Pair Ethernet PUR flexible, black [97B]

Conductor structure	1 x 2 x AWG 22/7, S/FTP
Conductor structure signal line	7x
AWG signal line	22
Conductor cross-section	2x 0.34 mm²
Wire diameter incl. insulation	1.65 mm
External cable diameter	5.10 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Tin-plated Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	white, blue
Thickness, outer sheath	0.55 mm
Twisted pairs	2 cores to the pair
Overall twist	1 pair with fillers twisted horizontally
Optical shield covering	80 %
Max. conductor resistance	≤ 59.4 Ω/km
Insulation resistance	≥ 5 GΩ*km
Wave impedance	100 Ω ±15 Ω (at 20 MHz)
Nominal voltage, cable	300 V
Minimum bending radius, fixed installation	4 x D
Smallest bending radius, fixed installation	21 mm
Flame resistance	According to FT-2
Ambient temperature (operation)	-20 °C ... 80 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-40 °C ... 85 °C
Resistance to oil	yes

Standards and regulations

Flame resistance	UL 94 V0
Resistance to oil	yes
Other resistance	UV resistant

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1183810

UL Recognized
Approval ID: File E335024

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	-	1.4 A	-	-

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	15.53 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com