


REL-SR- 24DC/2X1AU/2X2AU/FG - Safety relays



1158056

<https://www.phoenixcontact.com/us/products/1158056>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay with force-guided contacts in accordance with DIN EN 61810-3 (type A), input voltage 24 V DC, with multi-layer gold contact, 2 N/O contacts and 2 N/C contacts

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1158056 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | C460 |
| Product key | DK69DA |
| GTIN | 4063151164010 |
| Weight per piece (including packing) | 22.14 g |
| Weight per piece (excluding packing) | 22.14 g |
| Customs tariff number | 85364190 |
| Country of origin | CN |

1158056

<https://www.phoenixcontact.com/us/products/1158056>

Technical data

Product properties

| | |
|-------------------------|---|
| Product type | Single relay |
| Application | Forcibly guided contacts |
| Set comprises | 1148699 RIF-RPT-LDP-24DC/2X2/2X1/AU/FG |
| Operating mode | 100% operating factor |
| Mechanical service life | approx. 10^7 cycles |
| B _{10d} (AC15) | 810000 Cycles (AC15, 250 V / 0.5 A, 1 NO) |
| | 170000 Cycles (250 V / 2 A; 1 NO) |
| B _{10d} (DC13) | 318000 Cycles (DC13, 24 V / 1 A, 1 NO) |
| | 208000 Cycles (DC13, 24 V / 2 A, 1 NO) |

Insulation characteristics: Air clearances and creepage distances between the power circuits

| | |
|----------------------|--|
| Insulation | Basic insulation |
| | Safe isolation, reinforced insulation and 6 kV between the coil and the contact circuit and between the contacts 3-4, 5-6 to 7-8, 9-10 |
| Overvoltage category | III |
| Pollution degree | 2 |

Data management status

| | |
|------------------------------|------------|
| Date of last data management | 01.04.2026 |
|------------------------------|------------|

Electrical properties

| | |
|---|--|
| Maximum power dissipation for nominal condition | 0.36 W |
| Test voltage (Winding/contact) | 4 kV _{rms} (50 Hz, 1 min., winding/contact) |
| Test voltage (Contact/contact) | 2.5 kV _{rms} (50 Hz, 1 min., contact/contact) |

Air clearances and creepage distances between the power circuits

| | |
|--------------------------|----------|
| Rated insulation voltage | 250 V AC |
| Rated surge voltage | 4 kV |

Input data

Coil side

| | |
|--|-------------------------|
| Nominal input voltage U _N | 24 V DC |
| Input voltage range | 19.2 V DC ... 26.4 V DC |
| Input voltage range in reference to U _N | see diagram |
| Drive and function | monostable |
| Drive (polarity) | non-polarized |
| Typical input current at U _N | 15 mA |
| Typical response time | 10 ms |
| Typical release time | 5 ms |

Output data

REL-SR- 24DC/2X1AU/2X2AU/FG - Safety relays



1158056

<https://www.phoenixcontact.com/us/products/1158056>

Switching

| | |
|---|--|
| Contact switching type | 2 N/O contacts, 2 N/C contacts, force-guided |
| Type of switch contact | Single contact |
| Contact material | AgSnO, hard gold-plated |
| Maximum switching voltage | 250 V AC 300 V DC |
| Minimum switching voltage | 10 V |
| Limiting continuous current | 6 A |
| Maximum inrush current | 35 A (20 ms) |
| Min. switching current | 5 mA (10 V) |
| Interrupting rating (ohmic load) max. | 144 W (24 V DC) 100 W (48 V DC) 75 W (60 V DC) 55 W (110 V DC) 50 W (220 V DC) 1500 VA (250 V AC) |
| Switching capacity | 2 A (24 V (DC13)) 3 A (230 V, AC15) |
| Force-guided contacts in accordance with EN 61810-3 | Type A |

Connection data

| | |
|-------------------|--------------------------|
| Connection method | Plug / solder connection |
|-------------------|--------------------------|

Dimensions

Item dimensions

| | |
|--------|-------|
| Width | 13 mm |
| Height | 24 mm |
| Depth | 40 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|------------------------------|
| Degree of protection (Relay) | RT II |
| Degree of protection (Installation location) | IP54 (Installation location) |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | ≤ 2000 m |

Approvals

Corrosive gas test

| | |
|----------------|---|
| Identification | ISA-S71.04. G3 Harsh Group EN 60068-2-60 |
|----------------|---|

Standards and regulations

REL-SR- 24DC/2X1AU/2X2AU/FG - Safety relays



1158056

<https://www.phoenixcontact.com/us/products/1158056>

Air clearances and creepage distances between the power circuits


| | |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
| | EN 61810-1 |

Mounting

| | |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

Drawings

Diagram




Curve A: maximum continuous voltage at limiting continuous current

Curve B: minimum pick-up voltage for pre-excitation with U_N and limiting continuous current

1158056

<https://www.phoenixcontact.com/us/products/1158056>

Diagram




Interrupting rating

Curve 1: AC, ohmic load

Curve 2: DC, ohmic load

Diagram



Electrical service life

Diagram



Service life reduction factor with various cos phi

1158056

<https://www.phoenixcontact.com/us/products/1158056>



Permissible humidity for operation and storage.

The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures $\leq 0^\circ\text{C}$ must be prevented

Area B: Condensation at ambient temperatures $> 0^\circ\text{C}$ must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature $\leq 25^\circ\text{C}$.

REL-SR- 24DC/2X1AU/2X2AU/FG - Safety relays



1158056

<https://www.phoenixcontact.com/us/products/1158056>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1158056>



cUL Recognized
Approval ID: FILE E 228652



UL Recognized
Approval ID: FILE E 228652

1158056

<https://www.phoenixcontact.com/us/products/1158056>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001437 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

REL-SR- 24DC/2X1AU/2X2AU/FG - Safety relays



1158056

<https://www.phoenixcontact.com/us/products/1158056>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.832 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com