

# PV-FT-C4F-C-6-350-BK-SP-53 - Device connector front mounting



1158456

<https://www.phoenixcontact.com/us/products/1158456>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: SUNCLIX, color: black, number of positions: 1, rated voltage: 1000 V DC, rated current: 38 A, Connection method: Crimp, cable length: 350

## Commercial data

Item number	1158456
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	ABLBA
GTIN	4063151164553
Weight per piece (including packing)	29.1 g
Weight per piece (excluding packing)	28.272 g
Country of origin	DE

# PV-FT-C4F-C-6-350-BK-SP-53 - Device connector front mounting



1158456

<https://www.phoenixcontact.com/us/products/1158456>

## Technical data

### Notes

#### Safety note

Safety note

- **WARNING:** Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
- **WARNING:** Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
- **WARNING:** The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
- The products are suitable for applications in plant, controller, and electrical device engineering.
- Assembled products may not be manipulated or improperly opened.
- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).
- When using the product in direct connection with third-party manufacturers, the user is responsible.
- For operating voltages > 50 V AC, conductive connector housings must be grounded
- Ensure that the protective or functional ground has been properly connected.
- Observe the corresponding technical data. You will find information:
  - o On the product
  - o On the packing label
  - o In the supplied documentation
  - o Online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) under the product
- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.
- Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
- Operate the connector only when it is fully plugged in and interlocked.
- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the

# PV-FT-C4F-C-6-350-BK-SP-53 - Device connector front mounting



1158456

<https://www.phoenixcontact.com/us/products/1158456>

standards.

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

## Product properties

Product type	Panel feed-through
Product family	SUNCLIX
Number of positions	1

## Insulation characteristics

Protection class	II
Degree of pollution	2

## Dimensions

Width	21 mm
Height	21 mm
Length	49.1 mm

## Electrical properties

Rated voltage (III/2)	1500 V
Rated voltage	1000 V DC in accordance with IEC 62852:2014/AMD1:2020
Rated surge voltage	16 kV
Rated surge voltage (III/3)	16 kV
Rated current (6.0 mm <sup>2</sup> )	38 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current	50 A (in accordance with UL 6703)
Contact resistance	< 0.45 mΩ (depending on the mating connector used)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	100
Insertion force	< 45 N ±10 N

## Material specifications

Color	black
Color of the housing part	black
Material Seal	EPDM
Material Housing	PPE
Flammability rating according to UL 94	V0
Insulating material group	II
O-ring material	Silopren
Material for screw connection	PA
Outer sheath, material	PE-X

## Cable/line

# PV-FT-C4F-C-6-350-BK-SP-53 - Device connector front mounting



1158456

<https://www.phoenixcontact.com/us/products/1158456>

Cable length	350 mm
Cable type	AWM 3271/3820
Outer sheath, material	PE-X
External sheath, color	black

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66/IP68 (2 m / 24 h) (plugged in)
	IP20 (Not plugged in)
	IP66/IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-25 °C ... 50 °C

## Standards and regulations

Standards/specifications	IEC 62852:2014/AMD1:2020
--------------------------	--------------------------

# PV-FT-C4F-C-6-350-BK-SP-53 - Device connector front mounting




1158456

<https://www.phoenixcontact.com/us/products/1158456>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1158456>

 <b>TÜV Rheinland</b> Approval ID: R 60165002-0001				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	1500 V	38 A	-	2.5 - 6

# PV-FT-C4F-C-6-350-BK-SP-53 - Device connector front mounting



1158456

<https://www.phoenixcontact.com/us/products/1158456>

## Classifications

### ECLASS

ECLASS-13.0	27440107
ECLASS-15.0	27440107

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# PV-FT-C4F-C-6-350-BK-SP-53 - Device connector front mounting



1158456

<https://www.phoenixcontact.com/us/products/1158456>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)
SCIP	7d8d98b3-20f5-418b-b439-8591b19098b0

### EF3.1 Climate Change

CO2e kg	0.337 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)