

# FOC-17P24-17P24-GL03/35 - Connecting cable



1183987

<https://www.phoenixcontact.com/us/products/1183987>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M17 MPO series with preassembled FO plug assembly: 24-pos. plug-plug, multimode fiberglass G62.5/125 µm OM1, with screw connection, length of FO cable: 35 m, IP67 degree of protection after being inserted, fixed installation in cable ducts, underground cable ducts, and cable protection pipes for indoor/outdoor use

## Your advantages

- The connector is small and compact, and it has a maximum outer diameter of 21 mm, which enables high-density installation
- Prefabricated FO connection assembly, no fusion splicing required on site, plug and play
- IP67 degree of protection, stainless steel housing, ambient temperature -40 °C ... +85 °C, suitable for industrial applications and harsh environments
- Armored fiber FO cable for indoor and outdoor applications, low smoke and free of halogen, standard length can be ordered from 10 m ... 200 m, customized length on request
- The connector has integrated protective cover, so that it can be used on site conveniently

## Commercial data

Item number	1183987
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHBA
GTIN	4063151221492
Weight per piece (including packing)	2,935 g
Weight per piece (excluding packing)	2,935 g
Customs tariff number	85447000
Country of origin	CN

# FOC-17P24-17P24-GL03/35 - Connecting cable



1183987

<https://www.phoenixcontact.com/us/products/1183987>

## Technical data

### Product properties

Product type	Data cable preassembled
Number of positions	24

### Electrical properties

Transmission medium	Multi-mode fiberglass
---------------------	-----------------------

### Mechanical properties

Tensile strength short-term/long-term	1500 N / 800N
---------------------------------------	---------------

### Material specifications

Flammability rating according to UL 94	V0
Ferrule material	PPS
Outer sheath, material	LSZH

### Cable/line

Cable length	35 m
Cable weight	81.00 kg/km
Cable type	Multimode fiberglass
Cable type	Non-metal armored fiber optic cable for indoor/outdoor applications
External cable diameter	7.5 mm
Outer sheath, material	LSZH
External sheath, color	black
Smallest bending radius, fixed installation	90 mm
Tensile strength short-term/long-term	1500 N / 800N
Lateral pressure, long-term	300.00 N/cm
Halogen-free	according to IEC 60754-1

### FO cable

Number of fibers	12
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Attenuation	< 1.5 dB (1300 nm)
Transmission medium	Multi-mode fiberglass

# FOC-17P24-17P24-GL03/35 - Connecting cable



1183987

<https://www.phoenixcontact.com/us/products/1183987>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1183987>



**EAC**

Approval ID: 19060508

# FOC-17P24-17P24-GL03/35 - Connecting cable



1183987

<https://www.phoenixcontact.com/us/products/1183987>

## Classifications

### ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

### ETIM

ETIM 10.0	EC002700
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FOC-17P24-17P24-GL03/35 - Connecting cable



1183987

<https://www.phoenixcontact.com/us/products/1183987>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)