

# THERMOMARK GO.K - Thermal transfer printer



1184146

<https://www.phoenixcontact.com/us/products/1184146>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mobile thermal transfer printer for marking materials in cartridge format. The printer can print materials in continuous format up to a material width of 24 mm.

## Product description

The THERMOMARK GO.K handheld printer is ideal for fast identification on site. The thermal transfer printer is robust, easy to use, and offers versatile functions. It processes continuous media for terminal marking, cable and wire marking, equipment marking, and plant marking.

Scope of supply:

THERMOMARK GO.K, brief instructions

## Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- 8 different bar codes and over 300 symbols can be integrated; up to 20 projects can be created and stored directly on the device
- Printing of self-adhesive, non-sticky labels and shrink sleeves
- The THERMOMARK GO.K prints materials in cartridge format, which contain the material to be marked and the appropriate ink ribbon
- Intuitive user guidance thanks to a well-structured menu and direct input keys
- Alternative control via the PROJECT complete software



## Commercial data

Item number	1184146
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221

# THERMOMARK GO.K - Thermal transfer printer



1184146

<https://www.phoenixcontact.com/us/products/1184146>

GTIN	4063151223441
Weight per piece (including packing)	858.09 g
Weight per piece (excluding packing)	676.46 g
Customs tariff number	84433210
Country of origin	CN

## Technical data

### Product properties

Product type	Marking system
Scope of supply	THERMOMARK GO.K, brief instructions

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Device properties

Print width	24 mm
Print resolution	203 dpi
Operating system	Windows 10, Windows Server 2016, Windows Server 2019, Windows Server 2022

### Electrical properties

#### Supply

Supply voltage range	12 V DC
----------------------	---------

### Dimensions

Width	98 mm
Height	69 mm
Length	230 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C
---------------------------------	----------------

# THERMOMARK GO.K - Thermal transfer printer



1184146

<https://www.phoenixcontact.com/us/products/1184146>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1184146>



**cULus Listed**

Approval ID: E140403

# THERMOMARK GO.K - Thermal transfer printer



1184146

<https://www.phoenixcontact.com/us/products/1184146>

## Classifications

### ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

### ETIM

ETIM 10.0	EC001684
-----------	----------

### UNSPSC

UNSPSC 21.0	43212100
-------------	----------

# THERMOMARK GO.K - Thermal transfer printer



1184146

<https://www.phoenixcontact.com/us/products/1184146>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)