

IB IL RTD 4/NTC-ECO - Temperature module



1185434

<https://www.phoenixcontact.com/us/products/1185434>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Temperature measurement terminal, Analog RTD inputs: 4 (NTC, linear resistors), connection technology: 2-conductor, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector

Product description

The terminal is designed for use within an Inline station. It is used to acquire signals from resistive temperature sensors. The measured values are depicted in standardized representation format. Inline ECO terminals are approved for the temperature range from 0°C to +55°C. The electronics base and Inline connector are supplied as standard.

Your advantages

- 4 analog inputs
- Connection of sensors in 2-conductor technology
- Sensors supported: NTC, linear resistors
- Data format: standardized representation
- Diagnostic information in the process data word
- Linear input range from 0 kΩ to 100 kΩ

Commercial data

Item number	1185434
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI143
GTIN	4063151225704
Weight per piece (including packing)	83.76 g
Weight per piece (excluding packing)	69 g
Customs tariff number	85389099
Country of origin	DE

IB IL RTD 4/NTC-ECO - Temperature module



1185434

<https://www.phoenixcontact.com/us/products/1185434>

Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Interfaces

Inline local bus

Number of interfaces	2
Connection method	Inline data jumper
Transmission speed	500 kbps

System properties

Programming data (LocalbusSlave)

Length code (hex)	04
ID code (dec.)	126
Length code (dec)	04
Process data channel	64 bit
Input address area	8 Byte
Output address area	0 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	64 bit

Fieldbus data telegram

Required parameter data	1 Byte
Required configuration data	4 Byte

Input data

IB IL RTD 4/NTC-ECO - Temperature module



1185434

<https://www.phoenixcontact.com/us/products/1185434>

Analog:

Input name	Analog RTD inputs
Description of the input	Inputs for resistive temperature sensors
Number of inputs	4 (NTC, linear resistors)
Connection method	Inline connector
Connection technology	2-conductor
Note regarding the connection technology	shielded
A/D conversion time	typ. 120 ms
A/D converter resolution	24 bit
Tolerance, relative	typ. $\pm 0.15\%$ (of measuring range final value, at $T_A = 25^\circ\text{C}$) max. $\pm 0.35\%$ (of measuring range final value, at $T_A = 25^\circ\text{C}$)
Data formats	Standardized representation
Input filter	Digital filter
Input filter time	120 ms (per channel)
Nominal value of the current sources	10 μA (pulsed current, the data is valid during the sampling phase)
Linear resistance measuring range	0 Ω ... 100 k Ω
Process data update	< 10 ms
Protective circuit	Overload protection; max. ± 40 V DC, 1 min. Transient protection; Suppressor diode

Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet
Scope of supply	including Inline connector
Diagnostics messages	Failure of the internal I/O supply I/O error message sent to the bus coupler Checksum error I/O error message sent to the bus coupler

Electrical properties

Maximum power dissipation for nominal condition	0.95 W
---	--------

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 85 mA typ. 56 mA

Potentials: Supply of analog modules (U_{ANA})

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 14 mA typ. 7.3 mA

Electrical isolation/isolation of the voltage ranges

IB IL RTD 4/NTC-ECO - Temperature module



1185434

<https://www.phoenixcontact.com/us/products/1185434>

Test voltage: Bus logic (local bus, communications power)	500 V AC, 50 Hz, 1 min
Test voltage: Analog I/O	500 V AC, 50 Hz, 1 min
Test voltage: Functional ground	500 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL RTD 4/NTC-ECO - Temperature module

1185434


<https://www.phoenixcontact.com/us/products/1185434>

Drawings

Dimensional drawing



Connection diagram



Connecting the sensors

IB IL RTD 4/NTC-ECO - Temperature module



1185434

<https://www.phoenixcontact.com/us/products/1185434>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1185434>



cULus Listed

Approval ID: E238705

IB IL RTD 4/NTC-ECO - Temperature module



1185434

<https://www.phoenixcontact.com/us/products/1185434>

Classifications

ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

ETIM

ETIM 10.0	EC001596
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB IL RTD 4/NTC-ECO - Temperature module



1185434

<https://www.phoenixcontact.com/us/products/1185434>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I, 7(c)-II

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b28b05a2-cc96-4e10-ab43-dc958ead9af0

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com