

# VIP-PA-4X14/26/ 1,0M/1756/041 - Front adapter



1162506

<https://www.phoenixcontact.com/us/products/1162506>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP VARIOFACE front adapter, with connected system cables for ControlLogix® 1756 I/O. Up to 4 x 8 channels can be connected.

## Your advantages

- Individual I/O modules lock to the controller for connection security
- Disconnect lever aids in removal from I/O card
- Marking label can be attached
- Pluggable screw terminals on adapter for power connection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1162506       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C423          |
| Product key                          | DK232R        |
| GTIN                                 | 4063151173012 |
| Weight per piece (excluding packing) | 454 g         |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

1162506

<https://www.phoenixcontact.com/us/products/1162506>

## Technical data

### Product properties

|                |                        |
|----------------|------------------------|
| Product type   | Front adapter          |
| Product family | VARIOFACE Professional |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree     | 2  |

### Electrical properties

|   |           |
|---|-----------|
| Operating voltage (DC)                  | ≤ 60 V DC |
| Current (Per path)                      | ≤ 1 A     |
| Current (per group, positive terminals) | ≤ 8 A     |
| Current (per group, negative terminals) | ≤ 8 A     |

Supported controller: ALLEN-BRADLEY ControlLogix

|                   |            |
|-------------------|------------|
| Suitable I/O card | 1756-OB32  |
|                   | 1756-OV32E |

### Connection data

#### Controller level

|                   |   |
|-------------------|---|
| Connection method | Plug-in connection                      |
| Note              | Can be plugged onto 36-pos. I/O modules |

#### Field level

|                                  |                      |
|----------------------------------|----------------------|
| Connection in acc. with standard | IEC 60603-13         |
| Connection method                | IDC/FLK socket strip |
| Number of connections            | 4                    |
| Number of positions              | 14                   |
| Pitch                            | 2.54 mm              |

#### Supply

|                                  |  |
|----------------------------------|--|
| Connection method                | Push-in / plug connection                    |
| Stripping length                 | 9 mm   |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 26 ... 16                                    |

### Dimensions

#### Item dimensions

|        |            |
|--------|------------|
| Width  | 344.975 mm |
| Height | 47.352 mm  |
| Depth  | 56.345 mm  |

# VIP-PA-4X14/26/ 1,0M/1756/041 - Front adapter



1162506

<https://www.phoenixcontact.com/us/products/1162506>

## Cable

|        |     |
|--------|-----|
| Length | 1 m |
|--------|-----|

## Cable/line

### 14X0.14 [PVC]

|   |  |
|---|--|
| UL AWM Style                                  | 2464/1061  |
| Number of positions                           | 14   |
| Shielded                                      | no   |
| Cable type                                    | 14X0.14 [PVC]  |
| Conductor type                                | Round cable set  |
| Conductor structure signal line               | 7x 0.16 mm   |
| AWG signal line                               | 26   |
| Conductor cross-section                       | 14x 0.14 mm <sup>2</sup>   |
| Wire diameter incl. insulation                | 1 mm ±0.03 mm  |
| External cable diameter                       | 6.40 mm ±0.4 mm  |
| Outer sheath, material                        | Semi-rigid PVC   |
| External sheath, color                        | gray   |
| Conductor material                            | Tin-plated Cu litz wires   |
| Cable resistance                              | ≤ 145 Ω/km (20 °C)   |
| Insulation resistance                         | ≥ 20 MΩ*km (20 °C)   |
| Smallest bending radius, fixed installation   | 55 mm  |
| Smallest bending radius, movable installation | 104 mm   |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)  |
| Halogen-free                                  | no   |
| Flame resistance                              | IEC 60332-1-2 (raw cable)<br>VDE 0842, Part 332-1-2 (raw cable)<br>IEC 60332-3-22 (raw cable)<br>UL VW-1<br>CSA FT-1 |
| Resistance to oil                             | can withstand occasional splashes (raw cable)  |
| Cable type                                    | Front adapter with splitting cable for four modules  |

## Environmental and real-life conditions

### Ambient conditions

|   |                               |
|---|-------------------------------|
| Degree of protection                    | IP20                          |
| Ambient temperature (operation)         | 0 °C ... 60 °C                |
| Ambient temperature (storage/transport) | 0 °C ... 80 °C                |
| Altitude                                | ≤ 2000 m (Above sea level)    |
| Permissible humidity (operation)        | 0 % ... 95 % (non-condensing) |

## Standards and regulations

|                       |                |
|-----------------------|----------------|
| Standards/regulations | UL 61010-2-201 |
|-----------------------|----------------|

# VIP-PA-4X14/26/ 1,0M/1756/041 - Front adapter



1162506

<https://www.phoenixcontact.com/us/products/1162506>

## Notes

Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

# VIP-PA-4X14/26/ 1,0M/1756/041 - Front adapter




1162506

<https://www.phoenixcontact.com/us/products/1162506>

## Drawings

Circuit diagram



1162506

<https://www.phoenixcontact.com/us/products/1162506>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1162506>



**UL classified**

Approval ID: E238705



**cUL Classified**

Approval ID: E238705



**cUL Recognized**

Approval ID: E196811



**UL Recognized**

Approval ID: E196811

# VIP-PA-4X14/26/ 1,0M/1756/041 - Front adapter



1162506

<https://www.phoenixcontact.com/us/products/1162506>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242292 |
| ECLASS-15.0 | 27242292 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002584 |
|-----------|----------|

1162506

<https://www.phoenixcontact.com/us/products/1162506>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | c04eae45-3d50-418e-95db-600918826c6d |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)