

FOC-LC:PA-ST:PA-OM4:D01/1,5 - FO patch cable




1187025

<https://www.phoenixcontact.com/us/products/1187025>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO patch cable, degree of protection: IP20, cable length: 1.5 m, number of positions: 2, 10 Gbps, OM4



Your advantages

- Glass fiber optical, 8-shaped FO cable jumper
- Indoor use, suitable for FO distribution and termination devices
- Made of halogen-free flame-retardant material, RoHS compliant

Commercial data

Item number	1187025
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIBC
GTIN	4063151229221
Weight per piece (including packing)	30 g
Weight per piece (excluding packing)	30 g
Customs tariff number	85447000
Country of origin	CN

1187025

<https://www.phoenixcontact.com/us/products/1187025>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	2
Connection profile	SC duplex as per IEC 61754-20

Electrical properties

Transmission medium	Multi-mode fiberglass
Transmission speed	10 Gbps

Mechanical properties

Tensile strength short-term/long-term	70 N
---------------------------------------	------

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	LSZH

Dimensions

External dimensions

External diameter min.	2 mm
External diameter max.	4 mm

Connector

Connection 2

Type	Plug straight 2x ST
Degree of protection	IP20

Cable/line

Cable length	1.50 m
Cable weight	5.30 kg/km
Cable type	Multimode fiberglass
Cable type	Zip cord
Cable abbreviation	I-V(ZN)H
Cable structure	Figure 8 cable
External cable diameter	2.00 mm
Outer sheath, material	LSZH
External sheath, color	violet
Single wire, number of litz wires	2
Individual wire diameter	900 µm
Bending radius, long-term	50 mm
Bending radius short term/long term	30 mm
Smallest bending radius, fixed installation	30 mm

FOC-LC:PA-ST:PA-OM4:D01/1,5 - FO patch cable



1187025

<https://www.phoenixcontact.com/us/products/1187025>

Smallest bending radius, movable installation	7.5 mm
Tensile strength short-term/long-term	70 N
Lateral pressure, long-term	100.00 N/cm
Halogen-free	complying with IEC 60754-1/2
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034
Flame resistance	yes
Behavior in fire	No corrosive or toxic fumes

FO cable

Number of fibers	2
Fiber	50/125 µm
Fiber type	Multimode fiberglass 50/125 µm
Cable, attenuation	3.5 dB/km (850 nm) , 1.5 dB/km (1300 nm)
Attenuation	≤ 3.5 dB/km (with 850 nm)
Transmission medium	Multi-mode fiberglass

Standards and regulations

Behavior in fire	No corrosive or toxic fumes
Flame resistance	yes
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034

1187025

<https://www.phoenixcontact.com/us/products/1187025>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 10.0	EC002700
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1187025

<https://www.phoenixcontact.com/us/products/1187025>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	47bd2aa6-e0ae-4840-82fa-eef36822a3a1

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com