

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wall-mounted NEMA 4/4X (IP66) 316L stainless steel enclosure with surge protection for 120 V AC/DC power and two 24 V DC loops with 28 V DC MCOV

Your advantages

- Eligible for limited lifetime warranty (in some U.S. markets)
- Customizable: expand base unit with SPDs to suit your application
- Polycarbonate and 316L stainless steel enclosures available
- UL 1449 Listed SPD
- Single solution for power, data, and signal in one enclosure

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1191887 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL20 |
| Product key | CL1481 |
| GTIN | 4063151243494 |
| Weight per piece (including packing) | 3,460 g |
| Weight per piece (excluding packing) | 3.6 g |
| Country of origin | US |

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Set consists of

PLT-SEC-T3-120-FM-UT - Type 3 surge protection device

2907918

<https://www.phoenixcontact.com/us/products/2907918>



Type 2/3 surge protection, consisting of protective plug and base element, with integrated status indicator and remote signaling for single-phase power supply networks. Nominal voltage: 120 V AC/DC

PT 2X2-24DC-ST - Surge protection plug

2838228

<https://www.phoenixcontact.com/us/products/2838228>



PT protective connector with protective circuit for two 2-wire floating signal circuits. 24 V DC nominal voltage. HART-compatible.

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887


<https://www.phoenixcontact.com/us/products/1191887>

PT 2X2+F-BE - Surge protection base-element

2839224

<https://www.phoenixcontact.com/us/products/2839224>

Base element for protective plug PT with protective circuit for two 2-wire floating signal circuit, gas-filled surge arrester between the connections 3-4 (GND) and 9-10, for mounting on NS 35/7.5 and NS 35/15, housing width: 17.5 mm



BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Technical data

Notes

Trade restriction

| | |
|---------|--|
| CE note | The products are offered exclusively for export outside the EU and the European Economic Area. |
|---------|--|

Product properties

| | |
|--------------------------------|--|
| Product type | Surge protection for NEMA power supply units |
| Type | DIN rail module, two-section, divisible |
| Surge protection fault message | optical |
| EN type | T2 / T3 |
| Number of ports | One |

Electrical properties

| | |
|-----------------------|------------------|
| Nominal voltage U_N | 120 V AC (Power) |
| | 24 V DC (Signal) |


Indicator/remote signaling

| | |
|--------------------|--------------------------------|
| Connection name | Remote fault indicator contact |
| Switching function | Changeover contact |

Connection data

| | |
|---------------------------------------|---------------------|
| Screw thread | M3 |
| Tightening torque, min | 0.5 Nm |
| Conductor cross-section flexible min. | 0.2 mm ² |
| Conductor cross-section flexible max. | 2.5 mm ² |
| Conductor cross-section, rigid min. | 0.2 mm ² |
| Conductor cross-section, rigid max. | 4 mm ² |
| Connection method | Screw connection |
| Screw thread | M3 |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 152 mm |
| Height | 203 mm |
| Depth | 102 mm |

Material specifications

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

| | |
|------------------|--|
| Color | Steel/stainless steel color |
| Housing material | Stainless steel, 316L, electropolished |

Protective circuit

Power supplies

| | |
|-----------------------|--|
| Direction of action | L/N-PE & Signal Line-Shield-Earth Ground |
| Nominal voltage U_N | 120 V AC (TN-S) 120 V AC (TT) |

Information technology

| | |
|--|-----------------------|
| Nominal voltage U_N | 120 V AC (Power) |
| | 24 V DC (Signal) |
| Max. operating voltage U_{max} | 150 V AC (Power) |
| | 28 V DC (Signal) |
| Nominal current I_N | 20 A (Power) |
| | 450 mA (Signal) |
| Max. discharge current I_{max} (8/20) μ s | 10 kA (Power) |
| Max. discharge current I_{max} (8/20) μ s maximum (line-line) | 10 kA (Signal) |
| Max. discharge current I_{max} (8/20) μ s maximum (line-earth) | 10 kA (Signal) |
| Resistance per path | 2.2 Ω (Signal) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP66/NEMA 4X |
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | \leq 2000 mm |
| Permissible humidity (operation) | 5 % ... 95 % |

Approvals

UL specifications

| | |
|---|-------------|
| Maximum continuous operating voltage MCOV | 150 V AC/DC |
| Short-circuit current rating (SCCR) | 10 kA |
| Voltage protection rating VPR (L-N) | 700 V |
| Voltage protection rating VPR (L-G) | 1000 V |
| Voltage protection rating VPR (N-G) | 900 V |
| Voltage protection rating VPR (DC+) - (DC-) | 700 V |
| Voltage protection rating VPR (DC+) - G | 1000 V |
| Voltage protection rating VPR (DC-) - G | 900 V |
| UL type | type 2 |
| Nominal discharge current I_n | 5 kA |
| Maximum Circuit Breaker | 25.00 A |
| Maximum Surge Current per Phase | 20 A |

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Mounting

Mounting type

Panel mounting

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device




1191887

<https://www.phoenixcontact.com/us/products/1191887>

Drawings

Dimensional drawing




BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Connection diagram



Connections for power protection only are shown. For signal protection connection, refer to included article datasheet. Signal and power protection may be bonded through DIN rail.

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1191887>



UL Listed

Approval ID: FILE E 330181



cUL Listed

Approval ID: FILE E 330181

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27171203 |
| ECLASS-15.0 | 27171203 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000942 |
|----------|----------|

BXT-4XS-SEC-T3-120+2X2-24 - Surge protection device



1191887

<https://www.phoenixcontact.com/us/products/1191887>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, Not qualified for the European market |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com