

# EPC 1522 - Edge device



1185423

<https://www.phoenixcontact.com/us/products/1185423>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLCnext Industrial Edge Computer with Intel® Celeron® N3350 processor. This small form factor programmable edge device supports IEC 61131-3, MATLAB Simulink, C/C++, and is perfect for protocol converting, data collection, and cloud computing.

## Your advantages

- Local output of visualizations via DisplayPort
- Seamless support in PLCnext Engineer for OT programming
- Connection to PROFICLOUD
- Connection to PLCnext Store, for installing e.g. Node-RED, InfluxDB or Docker-Portainer
- Numerous protocols supported such as: http, https, FTP, SNTP, SNMP, SMTP, SQL, MySQL, DCP, etc.
- Two independent Ethernet interfaces
- High-level programming languages: IEC61131-3, C/C++, MATLAB Simulink
- Consistent graphical programming interfaces

## Commercial data

Item number	1185423
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBABE
GTIN	4063151225568
Weight per piece (including packing)	922.9 g
Weight per piece (excluding packing)	922.9 g
Customs tariff number	84715000
Country of origin	TW

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Controller
Product family	PLCnext Control
Type	Stand-alone

#### Computer data

Processor	Intel® Celeron® N3350 1.10 GHz
Trusted Platform Module	fTPM 1.2 (Encryption technology not Chinese)
RAM	4 GB LPDDR4
Data storage system	128 GB M.2-SSD, ~111 GB useable
Cooling	passive

#### Display

Display type	none
--------------	------

### System properties

Retentive data storage	Remanent data is not supported
Programmable under	High-level language IEC 61131-3

#### IEC 61131 runtime system

Program memory	8 Mbyte
Data storage system	12 Mbyte

#### Functionality

Programming languages supported	Instruction list (IL)
	Symbolic flowchart (SFC)
	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)
	C++
	C#
	Java
	Python®
	Simulink®

### Electrical properties

#### Supply

# EPC 1522 - Edge device



1185423

<https://www.phoenixcontact.com/us/products/1185423>

Supply voltage	24 V DC
----------------	---------

## Interfaces

Interfaces	1x DP++
	2x USB 3.0
	2x COM ports
LAN chipset	Intel® I210-AT

## Dimensions

### External dimensions

Width / Height / Depth	99 mm / 92 mm / 63 mm
------------------------	-----------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

## Approvals

### Conformity/Approvals

Conformance	CE-compliant
FCC	Title 47 Part 15 Subpart B:2018 Class A

## Mounting

Mounting type	DIN rail mounting
	Panel mounting

# EPC 1522 - Edge device



1185423

<https://www.phoenixcontact.com/us/products/1185423>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1185423>



### IECEE CB Scheme

Approval ID: US-39601-M1-UL



### UL Listed

Approval ID: E238705 D12:D1050



### cUL Listed

Approval ID: E238705 D12:D1050

# EPC 1522 - Edge device



1185423

<https://www.phoenixcontact.com/us/products/1185423>

## Classifications

### ECLASS

ECLASS-13.0	19200102
ECLASS-15.0	19200102

### ETIM

ETIM 10.0	EC001413
-----------	----------

### UNSPSC

UNSPSC 21.0	43211500
-------------	----------

# EPC 1522 - Edge device



1185423

<https://www.phoenixcontact.com/us/products/1185423>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ab1edff5-d112-4169-905a-8d78a97a5eb8

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)