

# SACB-C-H180-10/3-M8 HD - Connector hood



1197646

<https://www.phoenixcontact.com/us/products/1197646>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector hood, application: Standard, connection method: M8 socket Metal, number of slots: 10, number of positions: 3, slot assignment: single, status display: no, Universal; master cable connection: Pluggable screw connection 180°, shielding: no

## Your advantages

- Flexible, distributed bundling of signals in one master cable

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1197646       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF40          |
| Product key                          | AF3BCG        |
| GTIN                                 | 4063151257484 |
| Weight per piece (including packing) | 80.2 g        |
| Weight per piece (excluding packing) | 80.2 g        |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# SACB-C-H180-10/3-M8 HD - Connector hood



1197646

<https://www.phoenixcontact.com/us/products/1197646>

## Technical data

### Notes

|                              |   |
|------------------------------|---|
| Note regarding documentation | For details about the PCB connectors used, refer to the technical data for MC 1,5/10-STF-3,5 (1847204)  |
| Assembly note                | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |

### Product properties

|                     |                |
|---------------------|----------------|
| Product type        | Connector hood |
| Application         | Standard       |
| Number of positions | 3              |
| Number of slots     | 10             |

### Electrical properties

|   |         |
|---|---------|
| Max. operating voltage $U_{max}$        | 30 V DC |
| Nominal voltage $U_N$                   | 24 V DC |
| Rated current, total                    | 8 A     |
| Max. current carrying capacity per path | 2 A     |
| Current carrying capacity per slot      | 2 A     |

### Connection data

#### Conductor connection

|  |  |
|--|--|
| Sensor/actuator connection system                  | M8 socket                                    |
| Connection method                                  | Pluggable screw connection                   |
| Conductor cross-section Flexible signal line       | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section Flexible power supply      | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Connection cross section AWG Flexible signal line  | 26 ... 16                                    |
| Connection cross section AWG Flexible power supply | 26 ... 16                                    |
| Stripping length Signal line                       | 7 mm   |
| Stripping length of the sheath                     | 70 mm (Master cable)                         |
| Tightening torque, cover screw                     | 1 Nm   |

#### Connection assignment

|  |                   |
|--|-------------------|
| Slot/position = Wire color or connection | 1 / 4 (A) = 1 / 4 |
|  | 2 / 4 (A) = 2 / 4 |
|  | 3 / 4 (A) = 3 / 4 |
|  | 4 / 4 (A) = 4 / 4 |
|  | 5 / 4 (A) = 5 / 4 |
|  | 6 / 4 (A) = 6 / 4 |
|  | 7 / 4 (A) = 7 / 4 |
|  | 8 / 4 (A) = 8 / 4 |

# SACB-C-H180-10/3-M8 HD - Connector hood

1197646


<https://www.phoenixcontact.com/us/products/1197646>

|  |                                   |
|--|-----------------------------------|
|  | 9 / 4 (A) = 9 / 4                 |
|  | 10 / 4 (A) = 10 / 4               |
|  | 1-10 / 1 (+24 V) = U <sub>N</sub> |
|  | 1-10 / 3 (0 V) = 0 V              |

## Signaling

|                        |    |
|------------------------|----|
| Status display present | no |
|------------------------|----|

## Dimensions

|                          |  |
|--------------------------|--|
| Dimensional drawing      |  |
| Wrench size, union nut   | 24 mm  |
| Wrench size, counter nut | 24 mm  |

## Material specifications

|  |                    |
|--|--------------------|
| Material Housing   | PBT                |
| Material Cable gland                                     | PA 6 (Cable gland) |
| Seal material  | CR/NBR             |
| Material of contact, master cable side                   | CU alloy           |
| Material of the contact carrier on the master cable side | PA                 |
| Material of contact surface, master cable side           | tin-plated         |

## Cable/line

|                         |                            |
|-------------------------|----------------------------|
| External cable diameter | 6 mm ... 12 mm             |
| Connection method       | Pluggable screw connection |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | IP67             |
| Ambient temperature (operation) | -25 °C ... 80 °C |

# SACB-C-H180-10/3-M8 HD - Connector hood


1197646

<https://www.phoenixcontact.com/us/products/1197646>



## Drawings

Dimensional drawing




# SACB-C-H180-10/3-M8 HD - Connector hood

1197646

<https://www.phoenixcontact.com/us/products/1197646>

Schematic diagram



PCB connector positioning - the UN connection is on the end of the connector hood opposite the cable gland

# SACB-C-H180-10/3-M8 HD - Connector hood





1197646

<https://www.phoenixcontact.com/us/products/1197646>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1197646>

|  <b>UL Recognized</b><br>Approval ID: FILE E 118976 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 24 V                  | -                     | -                 | -                           |

|  <b>cUL Recognized</b><br>Approval ID: FILE E 118976 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 24 V                  | -                     | -                 | -                           |

# SACB-C-H180-10/3-M8 HD - Connector hood



1197646

<https://www.phoenixcontact.com/us/products/1197646>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440111 |
| ECLASS-15.0 | 27440111 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003558 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

# SACB-C-H180-10/3-M8 HD - Connector hood



1197646

<https://www.phoenixcontact.com/us/products/1197646>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)