

E-WML 6 (13X13)R - Wire-wrap label

1199663

<https://www.phoenixcontact.com/us/products/1199663>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire-wrap label, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E. WRAP, cable diameter range: 4 ... 6.1 mm, mounting type: adhesive, Number of individual labels: 4750, text field height: 12.7 mm, text field width: 12.7 mm

Product description

The self-laminating wrap-around labels in the E-WML... product family are designed for automated processing with the THERMOMARK E.WRAP applicator. After the printing and applying process, the markers adhere to the cable at a permanently defined position and the protective laminate protects the markers against dirt and abrasion. As the labels wrap tightly around the wires, they do not create any additional volume, so the wires can also be pulled through cable ducts, for example.

Your advantages

- For indoor and outdoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- Tight, bubble-free fit on the cable thanks to automatic winding
- For cylindrical objects, single wires, and cables

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1199663 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG15 |
| Product key | BG2311 |
| GTIN | 4063151261481 |
| Weight per piece (including packing) | 541.6 g |
| Weight per piece (excluding packing) | 408.6 g |
| Customs tariff number | 39191012 |
| Country of origin | FR |

E-WML 6 (13X13)R - Wire-wrap label



1199663

<https://www.phoenixcontact.com/us/products/1199663>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 4750 |
| Number of individual labels per row | 1 |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|----------|
| Width | 12.7 mm |
| Height | 31.75 mm |
| Depth | 0.1 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 12.7 mm |
| Text field height | 12.7 mm |

Material specifications

| | |
|-----------------------|------------------|
| Foil strength | 80 µm |
| Adhesive strength | 25 µm |
| Adhesive | Acrylic |
| Color | white (RAL 9010) |
| Material | PVC |
| Base element material | PVC |
| Components | Silicone-free |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 6.10 mm |
| | 4 mm ... 6.1 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 20 °C |
| Recommended humidity (storage/transport) | 40 % ... 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

Test for substances that would hinder coating with paint or varnish

| | |
|--|-------------------------|
| Testing for paint wetting impairment substances (LABS- | VDMA 24364-A1-L:2018-05 |
|--|-------------------------|

E-WML 6 (13X13)R - Wire-wrap label



1199663

<https://www.phoenixcontact.com/us/products/1199663>

| | |
|-------------|-------------|
| conformity) | |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilem test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature storage

| | |
|-------------------------|-----------------------|
| Specification | IEC 60068-2-2:2007-07 |
| Result | Test passed |
| Procedure | Test Bb |
| Duration | 96 h |
| Temperature for testing | 90 °C |

Moisture heat storage

| | |
|-------------------------|---------------------------------------|
| Specification | DIN EN 60068-2-30:2006-06 (following) |
| Result | Test passed |
| Duration | 96 h |
| Temperature for testing | 40 °C |
| Relative humidity | 90 % |

Temperature resistance

| | |
|---------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |

E-WML 6 (13X13)R - Wire-wrap label



1199663

<https://www.phoenixcontact.com/us/products/1199663>

| | |
|-------------------------------------|-------------|
| Acetone (99 %) [CAS No. 67-64-1] | Test passed |
|-------------------------------------|-------------|

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

E-WML 6 (13X13)R - Wire-wrap label



1199663

<https://www.phoenixcontact.com/us/products/1199663>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1199663>



cULus Recognized

Approval ID: MH67185Vol1sec1

E-WML 6 (13X13)R - Wire-wrap label



1199663

<https://www.phoenixcontact.com/us/products/1199663>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

E-WML 6 (13X13)R - Wire-wrap label



1199663

<https://www.phoenixcontact.com/us/products/1199663>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com