

CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool for processing ferrules according to DIN 46228-4, 0.5 mm² to 2.5 mm², equipped with pressure lock, magazine, cutting, stripping, twisting, and crimping unit.

Your advantages

- Robust and durable due to use of resistant plastics and annealed metals
- Multifunctional crimping pliers for the processing of Taped ferrules according to DIN 46228-4
- Integrated pressure lock ensures consistently high-quality crimping
- Up to 30 % time savings since the process steps required for assembling conductors can be carried out using only one tool
- Visualized process flows directly on the pliers simplify operation

Commercial data

Item number	1200101
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4055626042381
Weight per piece (including packing)	329 g
Weight per piece (excluding packing)	286.3 g
Customs tariff number	82032000
Country of origin	DE

CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Crimping tool
Compression	Indent crimp
Product property	Cutting, stripping, twisting, and crimping in one tool
	Tool-free magazine change for ferrules
	Length stop for stripping
	With pressure lock
Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²
AWG min	20
AWG max	14

Connection data

Conductor connection

Cross section range, metric	0.5 mm ² ... 2.5 mm ²
Cross section range AWG	20 ... 14
Stripping length	11 mm

Dimensions

Width	31.5 mm
Height	100 mm
Length	180 mm

Material specifications

Color	black
-------	-------

CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1200101>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX 4 IN 1 - Multifunctional tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	31.129 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com