

# CRIMPFOX 4 IN 1 SET - Crimping pliers set



1200102

<https://www.phoenixcontact.com/us/products/1200102>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool for processing ferrules according to DIN 46228-4, 0.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>, equipped with pressure lock, cutting, stripping, twisting, and crimping unit, with three magazines including a strip each of ferrules from 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, packaged in a robust plastic case

## Your advantages

- Robust and durable due to use of resistant plastics and annealed metals
- Multifunctional crimping pliers for the processing of Taped ferrules according to DIN 46228-4
- Integrated pressure lock ensures consistently high-quality crimping
- Up to 30 % time savings since the process steps required for assembling conductors can be carried out using only one tool
- Visualized process flows directly on the pliers simplify operation

## Commercial data

Item number	1200102
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4055626042398
Weight per piece (including packing)	735.2 g
Weight per piece (excluding packing)	727.7 g
Customs tariff number	82032000
Country of origin	DE

# CRIMPFOX 4 IN 1 SET - Crimping pliers set



1200102

<https://www.phoenixcontact.com/us/products/1200102>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type	Tool set
Type of packaging	Case
Compression	Indent crimp
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	2.5 mm <sup>2</sup>
AWG min	20
AWG max	14

### Connection data

Stripping length	8 mm
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section rigid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>

### Dimensions

Width	31.5 mm
Height	100 mm
Length	180 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX 4 IN 1 SET - Crimping pliers set



1200102

<https://www.phoenixcontact.com/us/products/1200102>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1200102>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 4 IN 1 SET - Crimping pliers set



1200102

<https://www.phoenixcontact.com/us/products/1200102>

## Classifications

### ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

### ETIM

ETIM 10.0	EC000149
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX 4 IN 1 SET - Crimping pliers set



1200102

<https://www.phoenixcontact.com/us/products/1200102>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	38.76 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)