

# CRIMPFOX CENTRUS 6S-NC - Crimping pliers



1202882

<https://www.phoenixcontact.com/us/products/1202882>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping tool, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm<sup>2</sup> ... 6 mm<sup>2</sup>, also for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, lateral insertion

## Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Clear view into the crimping area

## Commercial data

Item number	1202882
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4063151267377
Weight per piece (including packing)	453.2 g
Weight per piece (excluding packing)	368.74 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX CENTRUS 6S-NC - Crimping pliers



1202882

<https://www.phoenixcontact.com/us/products/1202882>

## Technical data

### Notes

General	DIN 46228-1, DIN 46228-4
---------	--------------------------

### Product properties

Product type	Crimping tool
Compression	Square crimp
Product property	Self-adjusting crimping die
	Clear view into the crimping area
	Compact, lightweight, and optimally balanced
	Low grip span
	Ergonomic two-component handle
	Low actuation force
	Suitable for TWIN ferrules
	Handle with non-slip pad
Tool-free unlockable pressure lock	

### Crimping position 1

Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	26
AWG max	10

## Connection data

### Conductor connection

Cross section range, metric	0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup> (2 x 0.5 mm <sup>2</sup> ... 2 x 4 mm <sup>2</sup> )
Cross section range AWG	26 ... 10 (2 x AWG 20 ... 2 x AWG 12)

## Dimensions

Width	65 mm
Height	22 mm
Length	175 mm

## Material specifications

Color	black/green
-------	-------------

# CRIMPFOX CENTRUS 6S-NC - Crimping pliers



1202882

<https://www.phoenixcontact.com/us/products/1202882>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX CENTRUS 6S-NC - Crimping pliers



1202882

<https://www.phoenixcontact.com/us/products/1202882>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)