

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 10.1-inch widescreen (16:9) XGA, PCAP display, software: Visu+ RT



Your advantages

- PCAP touch interface, ten-point multi touch control
- Fanless design
- Dual USB 2.0 ports
- Integrated Visu+ visualization software
- Ideal for use with PLCnext
- Configurable multifunction serial port



Commercial data

Item number	1190417
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR17
Product key	DRCADC
GTIN	4063151239176
Weight per piece (including packing)	2,260 g
Weight per piece (excluding packing)	2,100 g
Customs tariff number	84714100
Country of origin	TW

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Operator panel
Weight	2.1 kg

Computer data

Processor	Arm® Cortex®-A9, 800 MHz
Operating system	Windows® Embedded Compact 7
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

Display

Display type	25.9 cm / 10.2"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	500 cd/m ² typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	85.00 °
Reading angle right	85.00 °
Reading angle top	85.00 °
Reading angle bottom	85.00 °

Interfaces

Interfaces	2x USB 2.0
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1 x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

System properties

User software	Visu+
---------------	-------

System requirements

Runtime system	Visu+ Runtime
----------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Supply

Supply voltage	24 V DC \pm 20%
Supply voltage range	18 V ... 32 V
Power supply unit	24 V DC \pm 20 %
Max. current consumption	1.81 A (max. system configuration at 24 V DC)
Typical current consumption	0.79 A (max. system configuration at 24 V DC)

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Color (Housing)	white aluminium (RAL 9006)
Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 2.5 mm ²
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.25 mm ² ... 2.5 mm ² 0.25 mm ² ... 2.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 2.5 mm ²
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)
Shock	15g with 11 ms impulse
Vibration (operation)	1g

Dimensions

External dimensions

Width / Height / Depth	263 mm / 200 mm / 51 mm (Dimensions of the front plate)
------------------------	---

Installation dimensions

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Width / Height / Installation depth	252 mm / 189 mm / (Installation cutout)
-------------------------------------	---

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1190417>



IECEE CB Scheme

Approval ID: US-39088-UL



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Classifications

ECLASS

ECLASS-13.0	27330201
ECLASS-15.0	27330201

ETIM

ETIM 10.0	EC001412
-----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0f2dd68f-9bac-4906-a8d2-c2ccdf8bc5e2

EF3.1 Climate Change

CO2e kg	167.775 kg CO2e
---------	-----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com