

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 10.1-inch widescreen (16:9) XGA, PCAP display, software: Visu+ RT



Your advantages

- PCAP touch interface, ten-point multi touch control
- Fanless design
- Dual USB 2.0 ports
- Integrated Visu+ visualization software
- Ideal for use with PLCnext
- Configurable multifunction serial port

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1190417 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DR17 |
| Product key | DRCADC |
| GTIN | 4063151239176 |
| Weight per piece (including packing) | 2,260 g |
| Weight per piece (excluding packing) | 2,100 g |
| Customs tariff number | 84714100 |
| Country of origin | TW |

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|--------------|----------------|
| Product type | Operator panel |
| Weight | 2.1 kg |

Computer data

| | |
|---------------------|-----------------------------|
| Processor | Arm® Cortex®-A9, 800 MHz |
| Operating system | Windows® Embedded Compact 7 |
| Data storage system | Flash eMMC, 8 GB |
| Slots | 1x microSD |

Display

| | |
|-----------------------|--|
| Display type | 25.9 cm / 10.2"-TFT |
| Screen resolution | 1280 x 800 Pixel(s) (WXGA) |
| Touch technology | projective-capacitive (PCAP) |
| Display lighting type | LED |
| Brightness | 500 cd/m ² typical (adjustable) |
| MTBF | 50000 h |
| Color spectrum | 16.7 million colors |
| Reading angle left | 85.00 ° |
| Reading angle right | 85.00 ° |
| Reading angle top | 85.00 ° |
| Reading angle bottom | 85.00 ° |

Interfaces

| | |
|---------------------|---------------------------------------|
| Interfaces | 2x USB 2.0 |
| | 1x COM (RS-232/422/485) |
| Optional interfaces | Without optional interface |
| Network | 1 x Ethernet (10/100/1000 Mbps), RJ45 |
| Bus system | without bus system |

System properties

| | |
|---------------|-------|
| User software | Visu+ |
|---------------|-------|

System requirements

| | |
|----------------|---------------|
| Runtime system | Visu+ Runtime |
|----------------|---------------|

Electrical properties

| | |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Supply

| | |
|-----------------------------|---|
| Supply voltage | 24 V DC \pm 20% |
| Supply voltage range | 18 V ... 32 V |
| Power supply unit | 24 V DC \pm 20 % |
| Max. current consumption | 1.81 A (max. system configuration at 24 V DC) |
| Typical current consumption | 0.79 A (max. system configuration at 24 V DC) |

Real-time clock

| | |
|----------------|----------------------|
| Realtime clock | Yes (battery-backed) |
|----------------|----------------------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Front mounting |
|---------------|----------------|

Material specifications

| | |
|----------------------|------------------------------------|
| Color (Housing) | white aluminium (RAL 9006) |
| Material front plate | Aluminum (natural anodized) |
| Housing material | Aluminum cast alloy, powder-coated |

Connection data

| | |
|---|--|
| Connection method | Screw connection |
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm ² ... 2.5 mm ² 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Stripping length | 7 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------------------|
| Degree of protection | IP66 (front), IP20 (back) |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -25 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 85 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 85 % (non-condensing) |
| Shock | 15g with 11 ms impulse |
| Vibration (operation) | 1g |

Dimensions

External dimensions

| | |
|------------------------|---|
| Width / Height / Depth | 263 mm / 200 mm / 51 mm (Dimensions of the front plate) |
|------------------------|---|

Installation dimensions

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

| | |
|-------------------------------------|---|
| Width / Height / Installation depth | 252 mm / 189 mm / (Installation cutout) |
|-------------------------------------|---|

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1190417>



IECEE CB Scheme

Approval ID: US-39088-UL



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27330201 |
| ECLASS-15.0 | 27330201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001412 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43211900 |
|-------------|----------|

TP 6101-WXPS - Touch panel



1190417

<https://www.phoenixcontact.com/us/products/1190417>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-15 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 0f2dd68f-9bac-4906-a8d2-c2ccdf8bc5e2 |

EF3.1 Climate Change

| | |
|---------|-----------------|
| CO2e kg | 167.775 kg CO2e |
|---------|-----------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com