

# ZAP 25 T - Crimping tool, pneumatic



1203123

<https://www.phoenixcontact.com/us/products/1203123>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pneumatic crimping pliers, as table top version, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross-section 0.25 - 2.5 mm<sup>2</sup>

## Your advantages

- These crimping pliers have been specially developed for pre-assembling conductors
- The crimping process is activated by a foot valve
- Two integrated recesses allow quick access to the ferrules

## Commercial data

Item number	1203123
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3232
GTIN	4017918018092
Weight per piece (including packing)	2,421 g
Weight per piece (excluding packing)	2,421 g
Customs tariff number	84671900
Country of origin	DE

# ZAP 25 T - Crimping tool, pneumatic



1203123

<https://www.phoenixcontact.com/us/products/1203123>

## Technical data

### Product properties

Product type	Automatic crimping device
Compression	trapezoidal
Air consumption per compression	0.2 l
Pressure range	4.00 bar ... 6.00 bar
Product property	Start the crimping cycle using a foot pedal
	Duo press die for front and lateral conductor entry
	1 die nest
	Integrated part bins for ferrules
	Die width: 12 mm
	Insertion funnel allows for easy positioning

### Electrical properties

Frequency range	0 Hz
-----------------	------

### Connection data

#### Conductor connection

Cross section range, metric	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (2 x 0.5 mm <sup>2</sup> ... 2 x 1.5 mm <sup>2</sup> )
-----------------------------	---

### Dimensions

Width	140 mm
Height	70 mm
Length	200 mm

# ZAP 25 T - Crimping tool, pneumatic



1203123

<https://www.phoenixcontact.com/us/products/1203123>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1203123>



**EAC**

Approval ID: RU C-DE.AI30.B.01549



**EAC**

Approval ID: 0278662

# ZAP 25 T - Crimping tool, pneumatic



1203123

<https://www.phoenixcontact.com/us/products/1203123>

## Classifications

### ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

### ETIM

ETIM 10.0	EC002778
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# ZAP 25 T - Crimping tool, pneumatic



1203123

<https://www.phoenixcontact.com/us/products/1203123>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)