

# TP 6156-WHPS - Touch panel



1190421

<https://www.phoenixcontact.com/us/products/1190421>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 15.6-inch widescreen (16:9) HD, PCAP display, Software: Visu+ RT



## Your advantages

- PCAP touch interface, ten-point multi touch control
- Fanless design
- Dual USB 2.0 ports
- Integrated Visu+ visualization software
- Ideal for use with PLCnext
- Configurable multifunction serial port



## Commercial data

Item number	1190421
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR17
Product key	DRCADC
GTIN	4063151239053
Weight per piece (including packing)	2,260 g
Weight per piece (excluding packing)	2,100 g
Customs tariff number	84714100
Country of origin	TW

# TP 6156-WHPS - Touch panel



1190421

<https://www.phoenixcontact.com/us/products/1190421>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Operator panel
Weight	4.3 kg

#### Computer data

Processor	Arm® Cortex®-A9, 800 MHz
Operating system	Windows® Embedded Compact 7
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

#### Display

Display type	39.6 cm / 15.6"-TFT
Screen resolution	1920 x 1080 Pixel(s) (HD)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	450 cd/m <sup>2</sup>
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	85.00 °
Reading angle right	85.00 °
Reading angle top	85.00 °
Reading angle bottom	85.00 °

### Interfaces

Interfaces	2x USB 2.0
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1 x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

### System properties

User software	Visu+
---------------	-------

#### System requirements

Runtime system	Visu+ Runtime
----------------	---------------

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

# TP 6156-WHPS - Touch panel



1190421

<https://www.phoenixcontact.com/us/products/1190421>

## Supply

Supply voltage	24 V DC $\pm$ 20%
Supply voltage range	18 V ... 32 V
Power supply unit	24 V DC $\pm$ 20 %
Max. current consumption	1.81 A (max. system configuration at 24 V DC)
Typical current consumption	1.27 A (max. system configuration at 24 V DC)

## Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

## Mounting

Mounting type	Front mounting
---------------	----------------

## Material specifications

Color (Housing)	white aluminium (RAL 9006)
Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

## Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Stripping length	7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)
Shock	15g with 11 ms impulse
Vibration (operation)	1g

## Dimensions

### External dimensions

Width / Height / Depth	398 mm / 273 mm / 51 mm (Dimensions of the front plate)
------------------------	---

### Installation dimensions

# TP 6156-WHPS - Touch panel

1190421

<https://www.phoenixcontact.com/us/products/1190421>



Width / Height / Installation depth	388 mm / 263 mm / (Installation cutout)
-------------------------------------	---

# TP 6156-WHPS - Touch panel



1190421

<https://www.phoenixcontact.com/us/products/1190421>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1190421>



**IECEE CB Scheme**

Approval ID: US-39088-UL



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705

# TP 6156-WHPS - Touch panel



1190421

<https://www.phoenixcontact.com/us/products/1190421>

## Classifications

### ECLASS

ECLASS-13.0	27330201
ECLASS-15.0	27330201

### ETIM

ETIM 10.0	EC001412
-----------	----------

### UNSPSC

UNSPSC 21.0	43211900
-------------	----------

# TP 6156-WHPS - Touch panel



1190421

<https://www.phoenixcontact.com/us/products/1190421>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

### EF3.1 Climate Change

CO2e kg	167.775 kg CO2e
---------	-----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)