ZAP 25 T - Crimping tool, pneumatic

1203123

https://www.phoenixcontact.com/us/products/1203123

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pneumatic crimping pliers, as table top version, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross-section 0.25 - 2.5 mm^2

Your advantages

- These crimping pliers have been specially developed for pre-assembling conductors
- The crimping process is activated by a foot valve
- Two integrated recesses allow quick access to the ferrules

Commercial data

Item number	1203123
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3232
GTIN	4017918018092
Weight per piece (including packing)	2,421 g
Weight per piece (excluding packing)	2,908 g
Customs tariff number	84671900
Country of origin	DE

Technical data

Product properties

Product type	Automatic crimping device
Compression	trapezoidal
Air consumption per compression	0.2 l
Pressure range	4.00 bar ... 6.00 bar
Product property	Start the crimping cycle using a foot pedal
	Duo press die for front and lateral conductor entry
	1 die nest
	Integrated part bins for ferrules
	Die width: 12 mm
	Insertion funnel allows for easy positioning

Electrical properties

Frequency range	0 Hz

Connection data

Conductor connection

Cross section range, metric	0.25 mm² ... 2.5 mm² (2 x 0.5 mm² ... 2 x 1.5 mm²)

Dimensions

Width	140 mm
Height	70 mm
Length	200 mm

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1203123

EAC
Approval ID: RU C-DE.AI30.B.01549

EAC
Approval ID: 0278662

Classifications

ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

ETIM

ETIM 10.0	EC002778

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	70.719 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com