

# FOC-ADAPTER:LCD/LCD-MM - FO coupling



1207355

<https://www.phoenixcontact.com/us/products/1207355>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO coupling, degree of protection: IP20, number of positions: 2, material: Plastic, connection method: Coupling, cable outlet: straight, color: beige, Ethernet

## Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Versatile range of applications with an extended temperature range and various mounting options
- Suitable for use for all multimode classes
- Optimum compatibility with the FDX20 series splice boxes
- Future-proof, thanks to RoHS 2 conformity

## Commercial data

Item number	1207355
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	AB16
Product key	ABNIDA
GTIN	4063151275020
Weight per piece (including packing)	5.033 g
Weight per piece (excluding packing)	5.033 g
Customs tariff number	85367000
Country of origin	CN

1207355

<https://www.phoenixcontact.com/us/products/1207355>

## Technical data

### Product properties

Product type	Data plug
Type	LC
Number of positions	2
Connection profile	LC
Number of slots	2
Cable outlet	straight

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated surge voltage	0.8 kV
Attenuation	≤ 0.2 dB
Nominal current $I_N$	0.5 A
Transmission medium	FO

### Connection data

Connection method	Coupling
-------------------	----------

### Interfaces

Signal type/category	Ethernet
----------------------	----------

### Dimensions

Width	22 mm
Height	9.4 mm
Length	29.2 mm

### Mechanical characteristics

Ferrule diameter	1.25 mm
------------------	---------

### Material specifications

Color	beige
Color of the housing part	beige
Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy

### Cable/line

Cable type	Fiberglass
Signal type/category	Ethernet
External sheath, color	beige

# FOC-ADAPTER:LCD/LCD-MM - FO coupling



1207355

<https://www.phoenixcontact.com/us/products/1207355>

Tensile strength short-term/long-term	40 N
Flame resistance	yes

## FO cable

Number of fibers	2
Fiber	50/125 µm
Fiber type	Fiberglass
Attenuation	≤ 0.2 dB

## Mechanical properties

Tensile strength short-term/long-term	40 N
---------------------------------------	------

## Characteristics

Attenuation	≤ 0.2 dB
-------------	----------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	0 °C ... 50 °C
Resistance to UV radiation	no

## Standards and regulations

Flame resistance	yes
Standards/specifications	IEC 61754-20

# FOC-ADAPTER:LCD/LCD-MM - FO coupling



1207355

<https://www.phoenixcontact.com/us/products/1207355>

## Classifications

### ECLASS

ECLASS-13.0	19170116
ECLASS-15.0	19170116

### ETIM

ETIM 10.0	EC000752
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FOC-ADAPTER:LCD/LCD-MM - FO coupling



1207355

<https://www.phoenixcontact.com/us/products/1207355>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)