

1208054

<https://www.phoenixcontact.com/us/products/1208054>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor, design: Rail-mountable module, degree of protection: IP20, number of positions: 4, material: Metal, connection method: ODC connector, cable outlet: above and below, housing size: 1, color: gray, Ethernet

DIN rail distributor box 2x LC duplex to ODC 4-pos.

## Product description

FDX-20 series DIN rail distributor for Plug and Play connection, equipped with 2x LC Duplex couplings and 1x ODC 4-pos. socket, socket attached on the underside (upon request, the socket can also be attached on the top). Housing (2-part) prepared for DIN rail mounting through the rear-side adapter (this can also be mounted on the side)

## Your advantages

- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design
- Flexible DIN rail mounting possible in six positioning directions
- Suitable for industrial applications
- Reduced installation time with plug-and-play
- Pin assignment straight in line in a link
- Continuously reliable data connection, thanks to extensively tested components
- Snap-on mounting on standard DIN rails NS 35/7.5 or NS 35/15
- Transmission rate up to 1000 Mbps

## Commercial data

Item number	1208054
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHAC
GTIN	4063151275396
Weight per piece (including packing)	548.6 g
Weight per piece (excluding packing)	465.741 g
Customs tariff number	85367000
Country of origin	DE

1208054

<https://www.phoenixcontact.com/us/products/1208054>

## Technical data

### Product properties

Product type	Network distributor box
Type	Rail-mountable module
Sensor type	Ethernet
Number of positions	4
Connection profile	LC-Duplex
No. of conductors	4
Number of module slots	2
Number of slots	4
Protective cover	yes
Cable outlet	above and below

### Electrical properties

Attenuation	≤ 0.6 dB
Transmission medium	FO

### Connection data

#### Connection technology

Connection method	ODC connector
-------------------	---------------

### Dimensions

Width	40 mm
Height	130 mm
Depth	115 mm

#### Housing

Housing width	40 mm
---------------	-------

#### Mechanical characteristics

Ferrule diameter	1.25 mm
------------------	---------

### Material specifications

Color	gray
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics
Housing material	Metal
Housing surface material	Powder-coated, gray (metal housing)

### Cable/line

Cable type	Multimode fiberglass
Cable type	Fan out
External cable diameter	≤ 12.00 mm (of 6 mm)

1208054

<https://www.phoenixcontact.com/us/products/1208054>

	6 mm ... 12 mm
Individual wire diameter	2 mm

#### FO cable

Number of fibers	4
Fiber	GOF
Fiber type	Multimode fiberglass 62.5/125 µm
Transmission medium	FO

#### Characteristics

Attenuation	≤ 0.6 dB
-------------	----------

#### Environmental and real-life conditions

##### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

#### Mounting

Mounting type	DIN rail mounting
Assembly note	Option for flexible replugging of DIN rail adapter

1208054

<https://www.phoenixcontact.com/us/products/1208054>

## Classifications

### ECLASS

ECLASS-13.0

19170113

### ETIM

ETIM 9.0

EC001130

### UNSPSC

UNSPSC 21.0

43223300

1208054

<https://www.phoenixcontact.com/us/products/1208054>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)