

# NBC-M12MS/15,0-94L/R4AC - Network cable



1192092

<https://www.phoenixcontact.com/us/products/1192092>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT5e (1 Gbps), 8-position, TPE, highly flexible, turquoise, Plug straight M12, coding: A / IP65, on Plug straight RJ45 / IP20, cable length: 15 m

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1192092                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF15                           |
| Product key                          | AF1IHD                         |
| GTIN                                 | 4063151344245                  |
| Weight per piece (including packing) | 1,018 g                        |
| Weight per piece (excluding packing) | 22.22 g                        |
| Customs tariff number                | 85444290                       |
| Country of origin                    | US                             |

1192092

<https://www.phoenixcontact.com/us/products/1192092>

## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Product type        | Data cable preassembled |
| Application         | Standard, U.S. cables   |
| Sensor type         | Ethernet                |
| Number of positions | 8                       |
| Shielded            | yes                     |
| Coding              | A                       |

### Interfaces

|                      |                        |
|----------------------|------------------------|
| Bus system           | Ethernet               |
| Signal type/category | Ethernet CAT5e, 1 Gbps |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties

|                       |  |
|-----------------------|--|
| Nominal voltage $U_N$ | 48 V AC  |
|                       | 60 V DC (RJ45 30 V AC/57 V DC)   |
|                       | RJ45 30 V AC/57 V DC   |
| Nominal current $I_N$ | 2 A (Plug/socket in accordance with IEC 61076-2-101, cable technical data is to be observed) |
|                       | 1.5 A (RJ45)   |
| Transmission medium   | Copper   |
| Transmission speed    | 1 Gbps   |

### Connector

#### Connection 1

|                      |   |
|----------------------|---|
| Type                 | Plug straight M12 / IP65                                |
| Coding type          | A (Standard)  |
| Material             | CuZn (Contact)  |
|                      | Ni/Au (Contact surface)                                 |
|                      | TPU GF (Contact carrier)                                |
|                      | TPU, hardly inflammable, self-extinguishing (Grip body) |
|                      | Stainless steel (Screw connection)                      |
| Degree of protection | IP65  |

#### Connection 2

|              |                           |
|--------------|---------------------------|
| Type         | Plug straight RJ45 / IP20 |
| Handle color | gray                      |
| Material     | CuSn (Contact)            |
|              | Ni/Au (Contact surface)   |

# NBC-M12MS/15,0-94L/R4AC - Network cable



1192092


<https://www.phoenixcontact.com/us/products/1192092>

|                      |                      |
|----------------------|----------------------|
|                      | PC (Contact carrier) |
|                      | PA (Housing)         |
| Degree of protection | IP20                 |

## Cable/line

|              |      |
|--------------|------|
| Cable length | 15 m |
|--------------|------|

### Highly flexible Ethernet CAT5e [94L]

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |    |
| UL AWM Style                    | 2463 (80 °C / 600 V)   |
| Number of positions             | 8  |
| Shielded                        | yes  |
| Cable type                      | Highly flexible Ethernet CAT5e [94L]   |
| Conductor structure             | 4x2xAWG24/7; SF/UTP  |
| Conductor structure signal line | 7x 0.20 mm (7x32)  |
| AWG signal line                 | 24   |
| Conductor cross-section         | 4x 2x 0.2 mm <sup>2</sup>  |
| Wire diameter incl. insulation  | 1.2 mm   |
| External cable diameter         | 7.40 mm ±0.25 mm   |
| Outer sheath, material          | TPE  |
| External sheath, color          | turquoise  |
| Conductor material              | Tin-plated Cu litz wires   |
| Material wire insulation        | PE   |
| Single wire, color              | white/blue-blue, white/orange-orange, white/green-green, white/brown-brown   |
| Twisted pairs                   | 2 cores to the pair  |
| Overall twist                   | 4 pairs for core   |
| Optical shield covering         | 75 %   |
| Wave impedance                  | 100 Ω ±15 Ω (at 100 MHz)   |
| Cable impedance                 | 100 Ω ±15 Ω (at 1 ... 100 MHz)   |
| Nominal voltage, cable          | 600 V  |
| Test voltage                    | 2000 V   |
| Dynamic load capacity (bending) | Max. bending cycles: 1000000, Bending radius: 10 x D, Traversing path: 0.23 m, Traversing rate: 1.5 m/s, Acceleration: 20.5 m/s <sup>2</sup><br>Max. bending cycles: 10000000, Bending radius: 20 X D (126 cycles/min. at 20 °C) |
| Dynamic load capacity (torsion) | Torsion: 360 °/m (1 lb. load), Torsion cycles: 4800000, Torsional frequency: 71 cycles/min, Ambient temperature (operation): 20  |

# NBC-M12MS/15,0-94L/R4AC - Network cable



1192092

<https://www.phoenixcontact.com/us/products/1192092>

|                                       |   |
|---------------------------------------|---|
|                                       | °C  |
| Near end crosstalk attenuation (NEXT) | 50 dB (with 100 MHz (IEC 62153-4-9))                        |
| Return attenuation (RL)               | 20 dB (at 10 MHz (+6LOG))                                   |
|                                       | 26 dB (at 20 MHz)   |
|                                       | 26 dB (at 100 MHz (-5LOG))                                  |
| Flame resistance                      | VW-1  |
| Other resistance                      | Resistant to welding splashes (Abrasion and oil resistance) |
|                                       | UV resistant (CMX outdoor)                                  |
| Ambient temperature (operation)       | -40 °C ... 80 °C (Cable, flexible installation)             |

## Standards and regulations

### M12

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

# NBC-M12MS/15,0-94L/R4AC - Network cable



1192092

<https://www.phoenixcontact.com/us/products/1192092>


## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



RJ45 connector, IP20

1192092

<https://www.phoenixcontact.com/us/products/1192092>

Schematic diagram



Pin assignment M12 plug, 8-pos., A-coded, view plug side

# NBC-M12MS/15,0-94L/R4AC - Network cable

1192092

<https://www.phoenixcontact.com/us/products/1192092>




Schematic diagram



Connector pin assignment plug RJ45

Circuit diagram



Contact assignment of the M12 and RJ45 plug

# NBC-M12MS/15,0-94L/R4AC - Network cable



1192092

<https://www.phoenixcontact.com/us/products/1192092>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1192092>

|  <b>UL Listed</b><br>Approval ID: File E335024 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 60 V                  | 0.5 A                 | -                 | -                           |

|  <b>cUL Listed</b><br>Approval ID: File E335024 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 60 V                  | 0.5 A                 | -                 | -                           |

# NBC-M12MS/15,0-94L/R4AC - Network cable



1192092

<https://www.phoenixcontact.com/us/products/1192092>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# NBC-M12MS/15,0-94L/R4AC - Network cable



1192092

<https://www.phoenixcontact.com/us/products/1192092>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |   |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | bis(2-ethylhexyl) tetrabromophthalate covering any of the individual isomers and/or combinations thereof(CAS: 26040-51-7) |
|-------------------------------------|---|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)