

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Applicator for the efficient printing and application of E-WMS... shrink sleeves and marking sleeves on wires and cables in a single automated process step

Product description

To achieve maximum efficiency in wire and cable identification processes, combine a standard roll printer from the THERMOMARK E SERIES with the THERMOMARK E.SLEEVE applicator. This provides you with an automated printing and application system that enables you to achieve time savings of up to 75% compared to manual identification processes. The THERMOMARK E.SLEEVE cuts the ready-printed E-WMS... shrink sleeves and marking sleeves in continuous format to the appropriate length, opens the individual markers, and feeds them in as far as the removal position so that the user can apply the finished markers to the wire/cable very easily. This unique system enables the efficient and demand-oriented creation of custom marker lengths between 15 mm/0.59" and 51 mm/2.0". Automated identification of all types of cylindrical objects that have a diameter of between 0.8 mm/0.03" and 8.5 mm/0.33" is supported.

Scope of supply:

THERMOMARK E.SLEEVE, TM E.WIRE/E.SLEEVE-PR pressure roller (1259203), multilingual packing slip

Your advantages

- Time savings of up to 75% compared to manual printing and application processes
- Consistently high level of efficiency over the entire working day through intuitive handling, which helps reduce costs
- Planning accuracy with regard to productivity and quality: in the case of order peaks, productivity can be increased significantly using the same number of employees
- Reduction in the number of user errors through intuitive step-by-step guidance along the entire identification process as well as automatic data processing from CAE systems and other popular file formats for data exchange
- Cost efficiency by using shrink sleeves in continuous format
- No setup effort, thanks to automatic diameter adjustment
- Automatic object detection
- Shrink sleeve markers cut to variable lengths from 15 mm ... 51 mm
- For cylindrical objects with a diameter ranging from 0.8 mm ... approx. 8.5 mm
- Quick and easy mounting of the applicator on the roll printer via hexagon screw
- The applicator is connected via the D-SUB interface on the roll printer and is detected automatically by the software

THERMOMARK E.SLEEVE - Applicator



1192932

<https://www.phoenixcontact.com/us/products/1192932>



Commercial data

Item number	1192932
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG122Z
GTIN	4063151244699
Weight per piece (including packing)	3,600 g
Weight per piece (excluding packing)	2,440 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK E.SLEEVE - Applicator



1192932

<https://www.phoenixcontact.com/us/products/1192932>

Technical data

Product properties

Product type	Printing system accessories
Scope of supply	THERMOMARK E.SLEEVE, TM E.WIRE/E.SLEEVE-PR pressure roller (1259203), multilingual packing slip

Electrical properties

Supply

Supply voltage range	24 V DC
----------------------	---------

Dimensions

Width	241.7 mm
Height	144.6 mm
Depth	190.1 mm

THERMOMARK E.SLEEVE - Applicator



1192932

<https://www.phoenixcontact.com/us/products/1192932>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1192932>



cULus Listed

Approval ID: E140403



cULus Listed

Approval ID: E140403



EAC

Approval ID: KZ 27978

THERMOMARK E.SLEEVE - Applicator



1192932

<https://www.phoenixcontact.com/us/products/1192932>

Classifications

ECLASS

ECLASS-13.0	19140192
ECLASS-15.0	19140192

ETIM

ETIM 10.0	EC001675
-----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

1192932

<https://www.phoenixcontact.com/us/products/1192932>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a196fc90-ba92-4398-bb04-0e750ab553fd

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com