

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable



1196809

<https://www.phoenixcontact.com/us/products/1196809>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Socket straight M12, coding: A, on Plug straight M12, coding: A, cable length: 0.3 m, Wiring: 1 - 2, 2 - 4, 3 - 2S2, 4 - 4S2

Commercial data

Item number	1196809
Packing unit	1 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	AF1COA
GTIN	4063151254834
Weight per piece (including packing)	43.9 g
Weight per piece (excluding packing)	43 g
Country of origin	PL

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable



1196809

<https://www.phoenixcontact.com/us/products/1196809>

Technical data

Product properties

Product type	Distributor with cable
Number of positions	3
No. of cable outlets	2
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 10 \text{ G}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Socket straight M12
Number of positions	3
Coding type	A

Connection 2

Type	Plug straight M12
Number of positions	3

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable



1196809


<https://www.phoenixcontact.com/us/products/1196809>

Coding type	A
-------------	---

Cable/line

Cable length	0.3 m
--------------	-------

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	23 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm (Signal line)
External cable diameter	3.85 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation) approx. 0.50 mm (Outer cable sheath)
Overall twist	3 wires, twisted
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	19 mm
Smallest bending radius, movable installation	38 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 38 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable



1196809

<https://www.phoenixcontact.com/us/products/1196809>

	DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	hydrolysis and microbe resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable




1196809

<https://www.phoenixcontact.com/us/products/1196809>


Drawings

Dimensional drawing



Socket M12 x 1, Y distributor

Dimensional drawing




Plug, M12 x 1, straight, shielded

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable

1196809


<https://www.phoenixcontact.com/us/products/1196809>

Dimensional drawing



Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side


SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable



1196809

<https://www.phoenixcontact.com/us/products/1196809>

Schematic diagram




Pin assignment M12 plug, 4-pos., A-coded, view plug side

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable

1196809

<https://www.phoenixcontact.com/us/products/1196809>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable



1196809

<https://www.phoenixcontact.com/us/products/1196809>

Classifications

ECLASS

ECLASS-13.0	27060313
ECLASS-15.0	27060313

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-M12FY/2X0,3PUR/M12MS 24 - Sensor/actuator cable



1196809

<https://www.phoenixcontact.com/us/products/1196809>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com