

NS 35/15 PERF 2M NZ REF CUT - DIN rail



1210240

<https://www.phoenixcontact.com/us/products/1210240>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, similar to EN 60715, material: Steel, zinc plating, color: silver

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1210240 |
| Packing unit | 5 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE72 |
| Product key | BH8422 |
| GTIN | 4046356528573 |
| Weight per piece (including packing) | 1.26 g |
| Weight per piece (excluding packing) | 1.26 g |
| Customs tariff number | 72166190 |
| Country of origin | DE |

NS 35/15 PERF 2M NZ REF CUT - DIN rail



1210240


<https://www.phoenixcontact.com/us/products/1210240>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 35 mm |
| Hole width | 15 mm |
| Hole height | 6.2 mm |
| Depth | 15 mm |
| Length | 2000 mm |
| Drill hole spacing | 25 mm |

Material specifications

| | |
|----------|--------------|
| Color | silver |
| Material | Steel |
| Coating | zinc plating |

Standards and regulations

| | |
|-------|---------------------|
| Tests | similar to EN 60715 |
|-------|---------------------|

Electrical tests

Short-time withstand current

| | |
|---|-------|
| Max. permissible thermal nominal current for PEN function | 232 A |
|---|-------|

NS 35/15 PERF 2M NZ REF CUT - DIN rail




1210240

<https://www.phoenixcontact.com/us/products/1210240>

Drawings

Dimensional drawing



NS 35/15 PERF 2M NZ REF CUT - DIN rail



1210240

<https://www.phoenixcontact.com/us/products/1210240>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400602 |
| ECLASS-15.0 | 27400602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001285 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

NS 35/15 PERF 2M NZ REF CUT - DIN rail



1210240

<https://www.phoenixcontact.com/us/products/1210240>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 2.695 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com