

# CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm<sup>2</sup> ... 10 mm<sup>2</sup>, unlockable pressure lock, lateral entry

## Your advantages

- The way in which the handles and the die are arranged means that the ferrules can be fitted however the tool is held
- These compact crimping pliers have been designed to reduce effort when working

## Commercial data

Item number	1212045
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4046356455732
Weight per piece (including packing)	514.5 g
Weight per piece (excluding packing)	439.7 g
Customs tariff number	82032000
Country of origin	DE

# CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	Square crimp

#### Crimping position 1

Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	10 mm <sup>2</sup>
AWG min	25
AWG max	7

### Connection data

#### Conductor connection

Cross section range, metric	0.14 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Cross section range AWG	25 ... 7

### Dimensions

Length	175 mm
--------	--------

### Material specifications

Color	black
-------	-------

# CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212045>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX 10S - Crimping pliers



1212045

<https://www.phoenixcontact.com/us/products/1212045>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	12.528 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)