

# CRIMPFOX-RCI 1 - Crimping pliers



1212055

<https://www.phoenixcontact.com/us/products/1212055>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for insulated cable lugs, 0.14 ... 1.0 mm<sup>2</sup> (light green, red), oval crimp

## Your advantages

- They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied
- The color-coded dies clearly indicate the cross section
- Unlockable pressure lock
- Crimping pliers for cable lugs and connectors

## Commercial data

Item number	1212055
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3132
GTIN	4046356453851
Weight per piece (including packing)	436.45 g
Weight per piece (excluding packing)	436.45 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-RCI 1 - Crimping pliers



1212055

<https://www.phoenixcontact.com/us/products/1212055>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	Oval crimp
Product property	Unlockable pressure lock
	Color-coded dies

#### Crimping position 1

Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	0.25 mm <sup>2</sup>
AWG min	26
AWG max	24

#### Crimping position 2

Min. cross section	0.25 mm <sup>2</sup>
Max. cross section	0.5 mm <sup>2</sup>
AWG min	24
AWG max	22

#### Crimping position 3

Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
AWG min	22
AWG max	18

### Connection data

#### Conductor connection

Cross section range, metric	0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Cross section range AWG	26 ... 18

### Dimensions

Width	18 mm
Height	59 mm
Length	198 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX-RCI 1 - Crimping pliers


1212055

<https://www.phoenixcontact.com/us/products/1212055>



## Drawings

Product drawing



# CRIMPFOX-RCI 1 - Crimping pliers



1212055

<https://www.phoenixcontact.com/us/products/1212055>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212055>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-RCI 1 - Crimping pliers



1212055

<https://www.phoenixcontact.com/us/products/1212055>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-RCI 1 - Crimping pliers



1212055

<https://www.phoenixcontact.com/us/products/1212055>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)