CRIMPFOX 4 IN 1 SET - Crimping pliers set

1200102

https://www.phoenixcontact.com/us/products/1200102

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Tool for processing ferrules according to DIN 46228-4, 0.5 mm^2 to 2.5 mm^2, equipped with pressure lock, cutting, stripping, twisting, and crimping unit, with three magazines including a strip each of ferrules from 0.5 mm^2 ... 2.5 mm^2, packaged in a robust plastic case

Your advantages

- Robust and durable due to use of resistant plastics
and annealed metals
- Multifunctional crimping pliers for the processing of
Taped ferrules according to DIN 46228-4
- Integrated pressure lock ensures consistently high-quality crimping
- Up to 30 % time savings since the process steps required for assembling conductors can be carried out using only one tool
- Visualized process flows directly on the pliers simplify operation

Commercial data

Item number	1200102
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3511
GTIN	4055626042398
Weight per piece (including packing)	735.2 g
Weight per piece (excluding packing)	727.7 g
Customs tariff number	82032000
Country of origin	DE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Case
Compression	Indent crimp
Min. cross section	0.5 mm²
Max. cross section	2.5 mm²
AWG min	20
AWG max	14

Connection data

Stripping length	8 mm
Conductor cross-section flexible	0.5 mm² ... 2.5 mm²
Conductor cross-section rigid	0.5 mm² ... 2.5 mm²

Dimensions

Width	31.5 mm
Height	100 mm
Length	180 mm

Material specifications

Color	black

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1200102

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	38.76 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com