CRIMPFOX-FO 5,41 - Crimping pliers

1212099

https://www.phoenixcontact.com/us/products/1212099

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for fiber optics connectors, 3.25 mm, 3.84 mm, 5.41 mm, 5.00 mm, 4.52 mm, HEX crimp

Your advantages

- Lateral conductor entry
- Unlockable pressure lock

Commercial data

Item number	1212099
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3138
GTIN	4046356454001
Weight per piece (including packing)	678 g
Weight per piece (excluding packing)	678 g
Customs tariff number	82032000
Country of origin	SE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	HEX crimp
Product property	Low actuation force
	Long handle for cross-sections up to 50 mm²
	Ergonomic two-component handle
	Tool-free unlockable pressure lock
	Handle with non-slip pad
	Crimping force can be readjusted
	Fastening lug for safety tape

Crimping position 1

Crimping width	3.25 mm

Crimping position 2

Crimping width	3.84 mm

Crimping position 3

Crimping width	5.41 mm

Crimping position 4

Crimping width	5.00 mm

Crimping position 5

Crimping width	4.52 mm

Connection data

Conductor connection

Cross section range, metric	3.25 mm² ... 5.41 mm²

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

External dimensions

Outside diameter	3.25 mm ... 5.41 mm

Material specifications

Color	black

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212099

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com