

# NS 32 AL UNPERF 2000MM - DIN rail, unperforated



1201028

<https://www.phoenixcontact.com/us/products/1201028>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, G profile, color: silver-colored

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1201028       |
| Packing unit                         | 5 m           |
| Minimum order quantity               | 10 m          |
| Sales key                            | BE72          |
| Product key                          | BE7255        |
| GTIN                                 | 4017918017156 |
| Weight per piece (including packing) | 570 g         |
| Weight per piece (excluding packing) | 570 g         |
| Customs tariff number                | 76042990      |
| Country of origin                    | AT            |

# NS 32 AL UNPERF 2000MM - DIN rail, unperforated



1201028

<https://www.phoenixcontact.com/us/products/1201028>

## Technical data

### Product properties

|              |          |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

### Dimensions

|                     |         |
|---------------------|---------|
| Dimensional drawing |         |
| Width               | 32 mm   |
| Depth               | 15 mm   |
| Length              | 2000 mm |

### Material specifications

|          |                |
|----------|----------------|
| Color    | silver-colored |
| Material | Aluminum       |
| Coating  | uncoated       |

### Standards and regulations

|                                  |                     |
|----------------------------------|---------------------|
| Connection in acc. with standard | IEC / EN            |
| Tests                            | similar to EN 60715 |

### Electrical tests

#### Short-time withstand current

|   |                    |
|---|--------------------|
| Equivalent E-Cu cross-section                             | 70 mm <sup>2</sup> |
| Short-time current resistance 1s                          | 8.4 kA             |
| Max. permissible thermal nominal current for PEN function | 192 A              |

# NS 32 AL UNPERF 2000MM - DIN rail, unperforated


1201028

<https://www.phoenixcontact.com/us/products/1201028>



## Drawings

Dimensional drawing



# NS 32 AL UNPERF 2000MM - DIN rail, unperforated



1201028

<https://www.phoenixcontact.com/us/products/1201028>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400602 |
| ECLASS-15.0 | 27400602 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001285 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# NS 32 AL UNPERF 2000MM - DIN rail, unperforated



1201028

<https://www.phoenixcontact.com/us/products/1201028>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)